

Promonitor NRF560



Lợi ích:

- Remote monitoring and control for Proservo tank gauge
- Indication via two line illuminated display
- Operation via 3 optical keys (touch control)
- Programming matrix
- Protection class IP 67 housing
- Explosion proof for hazardous area mounting

Phạm vi ứng dụng: The Promonitor NRF560 is a monitoring unit for use with the Proservo series of tank gauges. Mounted at the tank side or up to 1,200 meters away (local HART connection). Promonitor provides indication of measured level, temperature data and operating status, and can send operating commands to the Proservo NMS5 from a convenient location.

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/NRF560

Tín năng và thông số kỹ thuật

Continuous / Liquids

Measuring principle

Level radar

Characteristic / Application

Convenient Remote Indicator and Operation panel

Supply / Communication

85-264 VAC

20-55 VAC/20-62 VDC

Continuous / Liquids

Ambient temperature

Standard:

-20 °C ... 60 °C

(-4 °F ... 140 °F)

Optional:

-40 °C ... 60 °C

(-40 °F ... 140 °F)

Communication

digital HART

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, TIIS, NEPSI

Thông tin bổ sung www.apsc.endress.com/NRF560