

TA540

Protection tube for temperature sensors

Designed for use with resistance or thermocouple thermometers in heavy duty applications.



Thông tin thêm và mức tính giá hiện tại:
www.apsc.endress.com/TA540

Lợi ích:

- The stem shape can be straight or stepped for fast response time
- A wide choice of pipe sizes, materials and process connections is available
- TA540 is an industry standard protection tube manufactured from pipe
- Extension, immersion length and total length can be chosen according to process requirements
- The process connection can either be threaded or flanged weld
- Special versions can be manufactured according to specifications
- The connection to the thermometer is a female thread

Tổng quan về thông số kỹ thuật

- **Max. process pressure (static)** 150 bar (2176 psi)
- **Maximum standard immersion length** 4.000 mm (157,48")

Phạm vi ứng dụng: This device is a metallic protection tube with threaded or flanged welded process connection. Thermometer connection is a NPT female thread. A wide range of flange sizes according to common standards and materials for this device is available. Ideally, this leads to a wide range of flexible installations in heavy duty applications.

Tín năng và thông số kỹ thuật

Thermowell

Measuring principleFabricated Thermowell

Characteristic / Application

metric style

various process connections

round extension

Head connection

internal thread:

1/2" NPT

G1/2"

M20x1,5

Maximum standard immersion length4.000 mm (157,48")

Thermowell

Process connection

thread:

1/2" NPT

3/4" NPT

1" NPT

M20x1,5

flange:

DN25 PN16 B1

DN25 PN40 B1

DN40 PN40 B1

DN50 PN40 B1

ASME 1" 150 RF

ASME 1" 300 RF

ASME 1" 600 RF

ASME 1 1/2" 150 RF

ASME 1 1/2" 300 RF

ASME 1 1/2" 600 RF

ASME 1 1/2" 600 RTJ

ASME 1 1/2" 600 RTJ

ASME 2" 300 RF

ASME 2" 600 RF

ASME 2" 300 RTJ

Thermowell

Thermowell root diameter

1/4" SCH40

1/2" SCH40

1/2" SCH80

3/4" SCH40

Medium contact material

1.4401 (316)

1.4749 (~446)

Wetted part finishing (Ra)

< 1.6 µm (63.00 µin)

Tip shape

straight

reduced

Temperature range

-200...1.100 °C (-328...2.012 °F)

Max. process pressure (static)

150 bar (2176 psi)

Max. process pressure at 400 °C

depends on process connection

Thông tin bổ sung www.apsc.endress.com/TA540