


# TST434

## Resistance thermometer

Comprehensive and common temperature measurement technology for almost all branches of industry



More information and current pricing:

[www.au.endress.com/TST434](http://www.au.endress.com/TST434)

### Benefits:

- Robust terminal heads according to DIN EN 50446 or stable plastic housings offer optimal protection from extreme ambient conditions
- Reliable, long term stable and accurate indoor or outdoor ambient temperature measurement
- Simple and fast wall mounting
- Optional head transmitter with easy selection: Analog output 4 to 20 mA, HART®, PROFIBUS® PA or FOUNDATION Fieldbus™

### Specs at a glance

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Max. process pressure (static)** at 20 °C: 1 bar (15 psi)
- **Operating temperature range** PT 100: -30 °C ...100 °C (-22 °F ...212 °F)

**Field of application:** The RTD thermometer is especially designed for monitoring the room temperature. The device with head transmitter is a complete unit ready for use with enhanced measurement accuracy and reliability compared to directly wired sensors. For ambient temperature measurements indoor or outdoor.

## Features and specifications

Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Thermometer****Characteristic / Application**

metric style

probe for ambient temperature measurement

without neck

---

**Thermowell / protection tube**

without (not intended to use with thermowell)

---

**Outer diameter protection tube / Insert**

20,0 mm (0,79")

---

**Material protection tube/ thermowell**

Aluminium

---

**Operating temperature range**

PT 100:

-30 °C ...100 °C

(-22 °F ...212 °F)

---

**Max. process pressure (static)**

at 20 °C: 1 bar (15 psi)

---

**Accuracy**

class A acc. to IEC 60751

class B acc. to IEC 60751

---

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

---

**Certification**

SIL (transmitter only)

More information [www.au.endress.com/TST434](http://www.au.endress.com/TST434)