

VARIVENT assembly for process photometers CUA261

Flow assembly with VARIVENT adapter for a variety of optical inline measurements



Mais informações e preço atual:

www.br.endress.com/CUA261

Benefícios:

- Allows installation of Endress+Hauser process photometers into processes where VARINLINE housings are used
- Hygienic process connection, suitable for cleaning-in-place (CIP) and sterilization-in-place (SIP), ensures highest product safety
- Wide range of window materials and optical path lengths for optimum adaption to every process
- Compliant with FDA and (EC) No 1935/2004

Especificações resumidas

- **Process temperature** 0 to 135°C (32 to 275 °F)
- **Process pressure** max. 11 bar abs. (159 psi abs.) at 25°C (77°F)

Campo de aplicação: CUA261 is the right choice for you if you want to install a process photometer into pipelines with VARIVENT connection, for example for measurement of absorption, color or turbidity. Select from multiple path lengths and window materials to ensure a perfect fit into your process. CUA261 is available as VARIVENT adapter for already existing housings or can be ordered as complete flow assembly with VARINLINE housing.

Características e especificações

Concentration

Measuring principle

UV absorbance

Concentration

Application

VARIVENT process connection for installation of the optical sensors:
OUSAF44/46, OUSAF12, OUSAF22 and OUSTF10

Material

Body: stainless steel 316L

Windows: Borosilicate, quartz or sapphire

O-rings: EPDM, silicone, FKM

Process temperature

0 to 135°C (32 to 275 °F)

Process pressure

max. 11 bar abs. (159 psi abs.) at 25°C (77°F)

Mais informações www.br.endress.com/CUA261