

Proline Prosonic Flow E 100 ultrasonic flowmeter

Economical Ultrasonic flowmeter with integrated temperature measurement



More information and current pricing:

www.casc.endress.com/9E1B

Benefits:

- Long-term stability – reliable, robust sensor
- Reducing further measuring point – multivariable device
- Dependable flow measurement – high turndown (200:1)
- Time-saving local operation without additional software and hardware – integrated web server
- Extended calibration intervals – integrated device verification due to Heartbeat Technology
- Easy commissioning – brief parameter explanations

Specs at a glance

- **Max. measurement error** Volume flow: $\pm 0.5\%$ o.r. $\pm 0.02\%$ o.f.s. for 0.5 to 10 m/s (1.6 to 33 ft/s) $\pm 0.07\%$ o.f.s. for flow velocities < 0.5 m/s (1.64 ft/s)
- **Measuring range** 0.025 to 5 m/s (0.02 to 16.4 ft/s) 0 to 6360 dm³/min (0 to 1680 gal/min)
- **Medium temperature range** 0 to 150° (17.8 to 302 °F)
- **Max. process pressure** PN 25 / ASME Cl. 150
- **Wetted materials** Measuring tube: 1.4301 (F304) Process Connection: 1.4571; 1.4404 (F316L); 1.0038 (S235JR); 1,4306 (F304L); 1.4307 (F304L); A105

Field of application: Measuring of demineralized water in utilities, for example in boiler condensate return lines, requires reliable devices. Prosonic Flow E 100 provides economical and accurate bidirectional flow measurement across all industries. With its integrated temperature measurement, Prosonic Flow E 100 proves to be a multivariable flowmeter for considerable additional value in your plant. Heartbeat

Technology ensures measurement reliability and enables extension of recalibration cycles.

Features and specifications

Liquids

Measuring principle

Ultrasonic flow

Product headline

Economical Ultrasonic flowmeter with integrated temperature measurement.

Bidirectional measuring of demineralized water applications for Utilities, e.g. boiler condensate return lines.

Sensor features

Long-term stability – reliable, robust sensor. Reducing further measuring point – multivariable device. Dependable flow measurement – high turndown (200:1).

Measurement accuracy up to $\pm 0.5\%$ (flow) or according to EN 1434 Cl. 2, $\pm 2.0\text{ }^{\circ}\text{C}$ ($\pm 3.6\text{ }^{\circ}\text{F}$) (temperature). Process temperatures up to $150\text{ }^{\circ}\text{C}$ ($302\text{ }^{\circ}\text{F}$). Entire meter housing made of stainless steel.

Transmitter features

Time-saving local operation without additional software and hardware – integrated web server. Extended calibration intervals – integrated device verification due to Heartbeat Technology. Easy commissioning – brief parameter explanations.

4-20 mA HART, pulse/frequency output. Local display for reading and monitoring available. Robust transmitter housing.

Nominal diameter range

DN 50 to 150 (2" to 6")

Wetted materials

Measuring tube: 1.4301 (F304)

Process Connection: 1.4571; 1.4404 (F316L); 1.0038 (S235JR); 1.4306 (F304L); 1.4307 (F304L); A105

Liquids

Measured variables

Volume flow, calculated mass flow, flow velocity, sound velocity, temperature

Max. measurement error

Volume flow:

- $\pm 0.5\%$ o.r. $\pm 0.02\%$ o.f.s. for 0.5 to 10 m/s (1.6 to 33 ft/s)

- $\pm 0.07\%$ o.f.s. for flow velocities < 0.5 m/s (1.64 ft/s)

Measuring range

0.025 to 5 m/s (0.02 to 16.4 ft/s)

0 to 6360 dm³/min (0 to 1680 gal/min)

Max. process pressure

PN 25 / ASME Cl. 150

Medium temperature range

0 to 150° (17.8 to 302 °F)

Ambient temperature range

-20 to 60 °C (-4 to 140 °F)

Sensor housing material

Stainless steel

Transmitter housing material

Compact:

AlSi10Mg, coated

Stainless steel, 1.4301

Degree of protection

Standard: IP66/67, Type 4X enclosure

With opened housing: IP20, Type 1 enclosure

Display/Operation

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

Liquids

Outputs

4 - 20 mA HART (active)
Pulse/frequency/switch output (passive)

Inputs

None

Power supply

DC 19.2 to 28.8 V

Hazardous area approvals

None

Product safety

CE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Calibration according to EN 1434 Class 2

Pressure approvals and certificates

PED

Material certificates

3.1 material

More information www.casc.endress.com/9E1B