

Memograph CVM40



More information and current pricing:

www.cz.endress.com/CVM40

Benefits:

- Measured value acquisition and data management in one device, suitable for all process photometers
- Highest data security and FDA conformity for user administration (FDA 21 CFR Part 11)
- Seamless system integration: Unique portfolio of communication standards suits every distributed control system (DCS)
- Simple and safe commissioning: Convenient setup multiplication to other devices with USB stick or SD-Card saves time and minimizes effort
- Menu-guided calibration streamlines maintenance of sensors
- Graphic visualization of measured values on color display
- Universal inputs for additional measuring values (temperature measurement, etc.)

Specs at a glance

- **Ingres protection** Front panel: IP65 (NEMA4) Rear panel: IP20

Field of application: Memograph CVM40 is a reliable, accurate transmitter and data manager for all process photometers. Connect up to two photometric sensors and get the readings on its graphical color display. Or choose from a broad selection of communication protocols to access it conveniently from any workplace. A security package according to FDA 21 CFR 11 ensures safe data logging and protects from unauthorized access. CVM40 is designed for intuitive operation and supports you with easy menu-guided calibration.

Features and specifications

Concentration

Measuring principle

Concentration

Application

Transmitter for in-line photometers and data manager

Measurement range

0-2,5 AU for Absorption

0-500 FTU or ppm for scattered light

Ingres protection

Front panel: IP65 (NEMA4)

Rear panel: IP20

More information www.cz.endress.com/CVM40