

# Promonitor NRF560

**Benefits:**

- Remote monitoring and control for Proservo tank gauge
- Indication via two line illuminated display
- Operation via 3 optical keys (touch control)
- Programming matrix
- Protection class IP 67 housing
- Explosion proof for hazardous area mounting

**Field of application:** The Promonitor NRF560 is a monitoring unit for use with the Proservo series of tank gauges. Mounted at the tank side or up to 1,200 meters away (local HART connection). Promonitor provides indication of measured level, temperature data and operating status, and can send operating commands to the Proservo NMS5 from a convenient location.

More information and current pricing:

[www.de.endress.com/NRF560](http://www.de.endress.com/NRF560)

## Features and specifications

### Continuous / Liquids

**Measuring principle**

Level radar

**Characteristic / Application**

Convenient Remote Indicator and Operation panel

**Supply / Communication**

85-264 VAC

20-55 VAC/20-62 VDC

## Continuous / Liquids

### Ambient temperature

Standard:

-20 °C ... 60 °C

(-4 °F ... 140 °F)

Optional:

-40 °C ... 60 °C

(-40 °F ... 140 °F)

---

### Communication

digital HART

---

### Certificates / Approvals

ATEX, FM, CSA, IEC Ex, TIIS, NEPSI

---

More information [www.de.endress.com/NRF560](http://www.de.endress.com/NRF560)