

Memograph M RSG40



详细信息和最新价格参见:

www.endress.com.cn/RSG40

优势:

- 显示屏设置：7" TFT显示屏提供最佳的现场读数功能。
- 安全：设有个人专用的访问权限和电子签名（(FDA 21 CFR 11)的安全包
- 灵活：自由选择显示模式，如仪表、流程图和圆形图示
- 清楚：报警管理，管理所有的有效报警、报警确认和历史报警
- 实用：安装深度158mm,前面板防护等级IP65,NEMA4；外接USB键盘操作，通过USB打印机打印
- 无限性：内置Web服务器,现场总线(Profibus, Modbus),通用标准协议和接口，例如支持USB, TCP/IP, OPC 和以太网
- 信息丰富：事件搜索，自动信号分析

产品规格参数

- **输入** 4...20 universal 6...14 digital
- **输出** 2 analog
- **显示** Wide-screen TFT
- **电源** 100...230 V AC +/-10% 24V (-10%; +15%) AC/DC
- **存储/记录** Internal memory SD card USB Stick

应用领域: 所有工艺过程安全、完整的记录和可视化。Memograph M RSG40拥有多种功能，采用模块化结构和直观操作概念。采用出色的7" TFT显示屏，可将过程数据以曲线或圆形图等或模拟流程图形式显示。Memograph M 配备完整的特殊应用软件包，其功能远远超过一台摄像机。

特征和规格

数据管理器和数据记录仪

测量原理

测量原理

Advanced Graphic Data Manager

数据管理器和数据记录仪

功能

The versatile solution with secure data recording, visualization and application-specific software packages.

输入

20 analog (max) (U, I, TC, RTD, frequency, pulse)

14 digital (max) (control, event and counting inputs)

输出

12 relays (max)

2 analog output (max) (I, pulse)

1 loop power supply

接口

RS232/485

Ethernet

USB

Modbus RTU/TCP Slave

Modbus RTU Master

PROFIBUS DP

存储/记录

internal memory

SD card

USB flash drive

显示

TFT 7" colour graphic display

外壳

panel mounting

desktop housing

field housing

数据管理器和数据记录仪**证书**

21 CFR Part 11
Milk pasteurisation approval
UL recognized
CSA

软件包

Batch software
Waster water software
Tele-alarm software
Gas-steam-heat calculation
Energy software (water + steam)
Waste water + storm overflow + Tele Alarm
Tele-alarm software + energy software (water + steam)

能量和应用管理器**测量原理**

测量原理

Energy manager

功能

Mass flow and energy calculation for Water and Steam.

计算结果

Not defined

应用数量

Not defined

数据存储

yes

计算标准

Not defined

能量和应用管理器**通信**

Not defined

电源

Not defined

回路供电

24...28 V DC

防护等级

IP30

输入

4...20 universal

6...14 digital

输出

2 analog

外形尺寸 (WxHxD)

195.2 x 149.2 x 227.1 mm (7.69" x 5.87" x 8.94")

操作

Jog shuttle on site and PC software ReadWin

显示

Wide-screen TFT

软件功能

Internal calculation for mass flow and energy

证书

CE

EAC

UL (US and CA)

热能量测量**测量原理**

热能量测量**功能**

Mass flow and energy calculation for Water and Steam.

证书

CE,
EAC,
UL (US and CA)

输入

4...20 universal, 6...14 digital

输出

2 analog

继电器输出

6...12

辅助电源

24...28 V DC

外形尺寸 (wxhxd)

195.2 x 149.2 x 227.1 mm
(7.69" x 5.87" x 8.94")

软件

Internal calculation for mass flow and energy

操作

Jog shuttle on site and PC software ReadWin

显示

Wide-screen TFT

其他

Memory inside, balancing

数据采集

测量原理

功能

Signal analysis
Interface / modem
OPC-Server
ReadWin 2000
Mathematic formula editor
energy package, water+steam

最大输入值

20 analog (U, I, TC, RTD, Frequency, Pulse)
14 digital (control, event and counting inputs)

最大输出值

12 Relay
2 Analog output (I, Pulse)
1 Power loop supply

接口

RS 232
RS 485
Ethernet
Modbus RTU
Modbus TCP
PROFIBUS DP
USB

存储/记录

Internal memory
SD card
USB Stick

显示

TFT 7" colour graphic display

数据采集

外壳

panel mounting
desktop housing
Field housing

电源

100...230 V AC +/- 10%
24V (-10%; +15%) AC/DC

证书

21 CFR 11
Milk pasteurisation approval
UL recognized
CSA GP

软件包

Batch programme
Waster water software
Tele-Alarm software
Gas-Steam-Heat calculation
Energy package + Water + Steam
Waste water + Storm overflow + Tele Alarm
Tele-Alarm software + Energy package + Water + Steam

更多信息 www.endress.com.cn/RSG40