

单通道型变送器

Liquiline Compact CM82

多参数现场型仪表，可以在各行业的在危险区和非危险区中使用



详细信息和最新价格参见:

www.endress.com.cn/CM82

优势:

- **操作简便**：使用现有平板电脑和智能手机操作和调试仪表。
- **快速可靠**：通过安全的Bluetooth蓝牙连接用户可以查看所有危险测量点或远程操作狭小安装点。
- **充分得益于Memosens数字式传感器技术的所有优势**：Memosens数字式传感器能够实现最安全的数据传输，具有最高测量值稳定性，使用十分便捷。
- **所需安装空间小**：两线制设备可以安装在安装装置内部，无需自带电源。
- **适用所有安装位置**：即使测量点需要直接耐受粉尘、水蒸气、雨、雪、炎热或严寒，CM82变送器始终是您的正确选择。

产品规格参数

- **输入** One channel transmitter
- **输出** 4 to 20 mA, HART
- **防护等级** IP67, IP68, NEMA Type 6

应用领域: Liquiline Compact CM82变送器小巧轻便，与Memosens数字式传感器搭配使用。狭长的外壳仅11 cm长和2 cm宽，配备直接安装传感器的连接接口，无需使用电缆。它与传感器搭配使用，能够安装在大多数装置中，安装更加便捷。通过独一无二的安全Bluetooth蓝牙连接，用户可以在平板电脑或智能手机上查看附近所有CM82测量点，远程便捷地操作。

特征和规格

pH

测量原理

玻璃电极

应用

All sectors, supporting all sensors with the blue Memosens plug-in head, environmental sector

安装

Connection of digital sensors with Memosens-Protocol

特点

Liquiline CM82 is a two-wire transmitter for all areas of process engineering

设计

Liquiline CM82 is optionally equipped with Bluetooth for comfortable remote commissioning via Smartphone/Tablets

材质

Housing, cover: Peek 151
Strain relief: EPDM
Axial ring Peek 450 G

外形尺寸

Diameter: 18.95 mm (0.75 inch)
Length: 114.7 mm (4.52 inch)

连接

Connection of digital sensors with Memosens-Protocol

防护等级

IP67, IP68, NEMA Type 6

输入

One channel transmitter

输出

4 to 20 mA, HART

pH

其他证书

CE, CSA C/US GP

ORP /氧化还原电位

测量原理

玻璃电极

应用

All sectors, supporting all sensors with the blue Memosens plug-in head, enviromental sector

安装

Connection of digital sensors with Memosens-Protocol

特点

Liquiline CM82 is a two-wire transmitter for all areas of process engineering

设计

Liquiline CM82 is optionally equipped with Bluetooth for comfortable remote commissioning via Smartphone/Tablets

材质

Housing, cover: Peek 151

Strain relief: EPDM

Axial ring Peek 450 G

外形尺寸

Diameter: 18.95 mm (0.75 inch)

Length: 114.7 mm (4.52 inch)

连接

Connection of digital sensors with Memosens-Protocol

防护等级

IP67, IP68, NEMA Type 6

ORP /氧化还原电位**输入**

One channel transmitter

输出

4 to 20 mA, HART

电导率**测量原理**

玻璃电极

应用

All sectors, supporting all sensors with the blue Memosens plug-in head, enviromental sector

安装

Connection of digital sensors with Memosens-Protocol

特点

Liquiline CM82 is a two-wire transmitter for all areas of process engineering

设计

Liquiline CM82 is optionally equipped with Bluetooth for comfortable remote commissioning via Smartphone/Tablets

材质

Housing, cover: Peek 151

Strain relief: EPDM

Axial ring Peek 450 G

外形尺寸

Diameter: 18.95 mm (0.75 inch)

Length: 114.7 mm (4.52 inch)

连接

Connection of digital sensors with Memosens-Protocol

电导率**防护等级**

IP67, IP68, NEMA Type 6

输入

One channel transmitter

输出

4 to 20 mA, HART

氧气**测量原理**

玻璃电极

应用

All sectors, supporting all sensors with the blue Memosens plug-in head, environmental sector

安装

Connection of digital sensors with Memosens-Protocol

特点

Liquiline CM82 is a two-wire transmitter for all areas of process engineering

设计

Liquiline CM82 is optionally equipped with Bluetooth for comfortable remote commissioning via Smartphone/Tablets

材质

Housing, cover: Peek 151

Strain relief: EPDM

Axial ring Peek 450 G

外形尺寸

Diameter: 18.95 mm (0.75 inch)

Length: 114.7 mm (4.52 inch)

氧气

连接

Connection of digital sensors with Memosens-Protocol

输入

One channel transmitter

输出

4 to 20 mA, HART

更多信息 www.endress.com.cn/CM82