

# Capacitance Point level detection Nivector FTI26

For all types of powdered and fine-grained solids especially in the food industry



## Avantajlar:

- Easy installation even in tight conditions or where access is restricted thanks to the compact design
- Fulfillment of all relevant hygienic requirements (3A, EHEDG, FDA, EG1935/2004); cleanable (IP69)
- IO-Link reduces costs and complexity with an easy configuration of the devices via engineering tools
- Best build-up performance in class and high sensitivity
- No individual adjustment to each medium necessary
- LED signalization for on-site function check

## Özelliklere genel bakış

- **Process temperature** -40°C...80°C (-40°F...176°F)

Fiyatı en az **€120,12**

05.07.2022 tarihinden itibaren fiyat

Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/FTI26](http://www.tr.endress.com/FTI26)

**Uygulama alanı:** The Nivector FTI26 is a cost-efficient point level switch for solids in the food industry and powder applications in all industries. The capacitance device convinces with the best build-up performance in class and a high sensitivity. All industry compliant certificates are available. In addition, the FTI26 is industry 4.0 ready with IO-Link communication.

## Özellikler ve şartlar

Point Level / Solids

**Measuring principle**  
Capacitive Solid

---

**Point Level / Solids****Characteristic / Application**

Compact for all types of powdered solids / small-grain  
bulk  
solids

---

**Specialities**

Active build-up compensation

---

**Supply / Communication**

12 V...30 VDC

---

**Ambient temperature**

-20°C...60°C  
(-4°F...140°F)

---

**Process temperature**

-40°C...80°C  
(-40°F...176°F)

---

**Main wetted parts**

PC, ECTFE  
"Protector"  
FDA listed material PBT-GF  
(according to 21 CFR 177.1660)

---

**Process connection**

G1

---

**Communication**

12 V...30 VDC  
IO-Link

---

**Safety approvals**

ATEX, CSA C/US, IEC Ex, EAC Ex

---

**Design approvals**

EN 10204-3.1

---

Point Level / Solids

Hygienic approvals  
3-A, EHEDG

---

Ayrıntılı bilgi [www.tr.endress.com/FTI26](http://www.tr.endress.com/FTI26)