

iTEMP TMT84

Temperature head transmitter

Transformation of sensor signals into standardized digital output signals for all industries



Lợi ích:

- Easy and standardized communication via PROFIBUS® PA Profile 3.02
- Meets the EMC requirements as per NAMUR NE 21 and the recommendations of NE 89 with regard to temperature transmitters with digital signal processing
- Straightforward design of measuring points in Ex-areas through FISCO/FNICO conformity in accordance with IEC 600079-27
- Safe operation in hazardous areas thanks to international approvals such as FM IS, NI, CSA IS, NI as well as ATEX Ex ia, Ex nA (Ex nL)
- High accuracy through sensor-transmitter matching
- Reliable operation with sensor monitoring and device hardware fault recognition
- Rapid no-tools wiring due to optional spring terminal technology

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/TMT84

Tổng quan về thông số kỹ thuật

- **Accuracy (Pt100)** $\leq 0,1 \text{ K}$ (Pt100) $\leq 0,18 \text{ }^{\circ}\text{F}$

Phạm vi ứng dụng: Unsurpassed reliability, accuracy and long-term stability in critical processes over all industries. The configurable transmitter not only transfers digital converted signals from RTD and TC sensors, it also transfers resistance and voltage signals using PROFIBUS® PA communication. High measurement point availability by means of sensor monitoring functions. Diagnostics information according to NAMUR NE 107. Optimization of the measurement accuracy by sensor-transmitter matching.

Tín năng và thông số kỹ thuật

Temperature transmitters**Measuring principle**Head transmitter

Input2 x RTD, TC, Ohm, mV

OutputPROFIBUS PA

Auxiliary power supply

9...32 V DC (PROFIBUS PA)

9...17,5 V DC (FISCO/FNICO)

CommunicationPROFIBUS PA

InstallationTerminal head form B

Accuracy(Pt100) $\leq 0,1$ K(Pt100) $\leq 0,18$ °F

Galvanic isolationyes

Temperature transmitters**Certification**

ATEX II2D Ex tb IIIC Db

ATEX II1G Ex ia IIC T4/T5/T6

ATEX II3G Ex nA IIC T6

ATEX II3D Ex tc IIIC Dc

ATEX II1G Ex ia IIC T6, II3D

ATEX II3G Ex nA IIC T6, II3D

ATEX II2G Ex d T6, II2D Ex tb
IIIC

FM+CSA IS, NI I/1+2/ABCD

FM IS, NI I/1+2/ABCD

CSA IS, NI I/1+2/ABCD

CSA XP, NI, DIP I, II, III/1+2/A-G

NEPSI Ex ia IIC T4/T5/T6

NEPSI Ex d IIC T6 Gb

NEPSI Ex nA IIC T4/T5/T6

IECEX Ex ia IIC T4/T5/T6

FM XP, NI, DIP I, II, III/1+2/A-G

IECEX Ex tb IIIC Db

IECEX Ex d T6 Gb, Ex tb IIIC Db

ATEX IECEX II1G Ex ia IIC T6 Ga

Temperature transmitters

Thông tin bổ sung www.apsc.endress.com/TMT84