

## Field Xpert SMT70

### Universal, high-performance tablet PC for device configuration



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/SMT70](http://www.apsc.endress.com/SMT70)

#### Lợi ích:

- High-performance, robust tablet with large 11.6" display and a battery runtime of up to 14 hours.
- Touch-enabled device configuration software with a direct link to the Netilion Platform for optimized plant asset management.
- Pre-installed device driver libraries for all of the important industrial protocols.
- Fast connection to devices with a single click thanks to automatic hardware detection, Online application software and DTM/Drivers update service offers new functionality and maximum security.
- Integrated Heartbeat Verification incl. PDF documentation.
- Connection to Endress+Hauser Bluetooth and WLAN devices - perfect for difficult-to-access instruments.
- Recommendation: The **Library** application is a valuable supplement for Field Xpert. Library saves and organizes all your documents generated with Field Xpert in the Endress+Hauser Cloud making everything safe, up to date and available everywhere.

#### Tổng quan về thông số kỹ thuật

- **Input Camera:**
  - 5 MP camera on the back with auto focus and LED flash with 1500 mcd
  - 2 MP camera on the front
- **Scanner:**
  - 1D/2D barcode scanner

**Phạm vi ứng dụng:** The Field Xpert SMT70 tablet PC for device configuration enables mobile plant asset management in hazardous (Ex zone 2) and non-hazardous areas. It is suitable for commissioning and maintenance staff to manage Endress+Hauser and third-party field instruments with digital communication interface. This tablet PC is designed as a complete solution that comes with pre-installed driver

libraries and is an easy-to-use, touch-enabled tool used to manage field instruments during their entire life cycle.

## Tín năng và thông số kỹ thuật

### Fieldbus components

#### Measuring principle

Device configurator

#### Function

The Field Xpert SMT70 tablet PC for universal device configuration supports protocols such as HART, PROFIBUS DP/PA, FOUNDATION Fieldbus, Modbus, and Endress+Hauser service protocols (CDI, ISS, IPC and PCP). The devices can be connected directly via a suitable interface e.g. a modem (point-to-point) or a bus system (point-to-bus).

#### Input

Camera:

- 5 MP camera on the back with auto focus and LED flash with 1500 mcd
- 2 MP camera on the front

Scanner:

- 1D/2D barcode scanner

#### CPU

Intel Core i5-5200U (2,2...2,7 GHz)

#### Memory

- 8 GB with DDR3L adapter
- 256 GB SSD M2-SATA robust version
- Micro SD card slot, support for SDHC/SDXC

## Fieldbus components

### Power supply

Replaceable, rechargeable lithium polymer battery, 11.1 VDC, 4100 mAh (45 Wh)/7800 mAh (86 Wh) (optional)

---

### Dimensions (WxHxD)

298.5 mm x 192 mm x 20 mm

(11.4 in x 7.48 in x 0.78 in)

---

### Screen size

- 11.6" LCD display, with Gorilla Glass protector
  - Capacitive multi-touch screen
  - Optical bonding, sunlight readable, LCD (730 Nit)
  - Ambient light sensor
- 

### Resolution

1366 x 768 pixels

---

### Communication interface

- 2 x USB 3.0
  - Intel Wireless AC7260 802.11 a/b/g/n/ac, DUAL Band WLAN
  - Bluetooth 4.0 BLE, Class 1
  - 4G LTE WWAN + 12 channel GPS (optional)
- 

### Operation

Operating system:

Windows 10 IoT Enterprise

---

## Fieldbus components

### **Configuration**

Touch-enabled device configuration software optimized for Field Xpert. The software supports protocols such as HART, PROFIBUS DP/PA, FOUNDATION Fieldbus, Modbus, and Endress+Hauser service protocols (CDI, ISS, IPC and PCP) and includes more than 2,700 pre-installed device and communication drivers.

---

### **Optional**

4G LTE WWAN + 12 channel GPS

---

## Fieldbus components

### Certificates

Degree of protection:

- IP65

Shock resistance:

- MIL-STD 810G 516.6 Procedure IV

Electromagnetic Compatibility:

Interference conformance to

- EN 55022: 2010+ AC: 2011
- EN 55022 Class B
- EN 61000-3-2
- EN 61000-3-3

Interference immunity to

- EN 55024: 2010
- IEC 61000-4-2
- IEC 61000-4-3
- IEC 61000-4-4
- IEC 61000-4-5
- IEC 61000-4-6
- IEC 61000-4-8
- IEC 61000-4-11

Hazardous area approval:

## Fieldbus components

---

Thông tin bổ sung [www.apsc.endress.com/SMT70](http://www.apsc.endress.com/SMT70)