

# RIA16

## Loop-powered indicator

Excellent readable indication of 4...20 mA signal with trend bar graph for a better process overview



### Benefícios:

- Display of 4 to 20 mA measured values
- 5-digit measured value display with dimension, bar graph and backlight
- No external power supply required
- Versions: Fiber glass reinforced plastic respectively aluminum for Ex-applications
- Easy 3-key operation; or configuration with FieldCare PC software; or configuration without power supply using setup box
- International approvals; marine approval
- Allows the HART® transmission protocol to pass unimpeded

### Especificações resumidas

- **Input** 1 x analogue 4...20 mA
- **Output** 1 x open collector
- **Output** 1 x open collector
- **Display** LCD 26 mm (1.02") 5-digit Bargraph Plain text display
- **Power Supply** Loop powered

a partir de **R\$ 4.742,44**

Preço a partir de 05.08.2021

Mais informações e preço atual:

[www.br.endress.com/RIA16](http://www.br.endress.com/RIA16)

**Campo de aplicação:** The indicator shows the measured signal on the large, backlit display. A bar graph indicates the value graphically for a quick process overview. An editable plain text field displays further information like engineering unit or TAG. Limit value infringement is also signaled and an open collector can be switched. The indicator is powered directly from the 4...20 mA loop and doesn't need a separate power supply. For applications in hazardous areas the device is available with Ex approvals.

---

## Características e especificações

---

### Acquisition / Evaluation

**Measuring principle**Display

---

**Function**Display

---

**Certification**

UR C/US

CSA GP

ATEX Ex i

FM USA NI

FM USA DIP

CSA NI

CSA DIP

Marine approval

---

**Input**1 x analogue 4...20 mA

---

**Output**1 x open collector

---

**Auxiliary power supply / Loop power supply**Loop powered

---

## Acquisition / Evaluation

**Dimensions (wxhxd)**

Field housing:

199 x 133 x 96 mm

(7.83" x 5.24" x 3.78")

**Operation**

3 keys interface on electronics + PC interface

FieldCare

**Display**

LCD 26 mm (1.02")

5-digit

Bargraph

Plain text display

## Process indicator &amp; control units

**Measuring principle**

Loop powered indicators

**Measuring principle**

Loop-powered field indicator

**Function**

Display

**Process indicator & control units****Display**

LCD 26 mm (1.02")

5-digit

Bargraph

Plain text display

---

**Power Supply**Loop powered

---

**Input**1 x analogue 4...20 mA

---

**Output**1 x open collector

---

**Output**1 x open collector

---

**Software functions**Not defined

---

Process indicator & control  
units

**Certificates**

UR C/US

CSA GP

ATEX Ex i

FM USA NI

FM USA DIP

CSA NI

CSA DIP

EAC

Marine approval

---

**SIL**

Not defined

---

**Panel mounting**

field

---

Mais informações [www.br.endress.com/RIA16](http://www.br.endress.com/RIA16)