

FDM软件MS21，现场数据管理器软件 管理和显示数据的报告软件（多用户版）



优势:

- 提供自动生成报告、打印报告、输出报告、读取数据、存储数据、加密输出、生成PDF服务
- 创建报告和模板
- 通过在线接口或从储存媒介中读取测量值：输出/输入数据
- SQL数据库/防篡改的加密数据存储方式
- 在线显示瞬时数值（“实时数据”）
- 提供下列软件版本：专业版

详细信息和最新价格参见:

www.endress.com.cn/MS21

应用领域: FDM应用软件包具有集中数据管理功能，并能够显示存储的数据。它可以对存储的过程数据进行完整归档和防篡改保护，例如测量值或诊断事件。提供连接设备的“实时数据”。FDM将数据存储于SQL数据库中，以防数据被篡改。支持以下数据库：PostgreSQL（软件光盘内提供此数据库）、Oracle或Microsoft SQL服务器。多用户版软件：允许多个用户同时使用软件，用户数量由许可证数量确定。

特征和规格

软件

测量原理

其他专业知识

软件**应用任务**

Data management
Documentation & reports
Process monitoring & visualization

应用场合

Multi-User License
Field Data Manager (FDM) is a software to store and visualize historical data read out measured data via online interface or from mass storage create reports and templates export / import data.
Automatic service for report generation printing reports read out of data storing of data secure export PDF generation is possible, too.
User management and audit trail enable working according to FDA 21CFR Part 11.
The software is available as Essential Version, free-of-charge with restricted functionality or as Professional Trial Version with full functionality but with a time restriction of 60 days (+30 on request). The Professional Version with full functionality can be purchased via a multi-User license.

软件**操作系统**

Windows 2003 Server R2 SP2 Standard, Enterprise (32 Bit)
Windows 2008 Server (32/64 Bit)
Windows 2012 Server (32/64 Bit)
Windows 2016 Server (32/64 Bit)
Windows 2019 Server (32/64 Bit)
Windows XP SP3 (32 Bit)
Windows XP SP2 (32 Bit)
Microsoft Vista (32 Bit)
Windows 7 (32/64 Bit)
Windows 8; Windows 8.1 (32/64 Bit)
Windows 10 (32/64 Bit)
Windows.NET 2.0 SP1

处理器型号

Pentium 4 (≥ 2 GHz)
Pentium M (≥ 1 GHz)
AMD (≥ 1.6 GHz)

主存储器

At least 1 GB

硬盘容量

Disk space needed: At least 20 GB

显示器分辨率和显示

1024x768 pixel

其他

PostgreSQL
Oracle Version 8i or higher
Microsoft SQL Server Version 2005 or higher
CD-ROM drive

软件

注册商标

Microsoft

Windows

Windows XP

Windows 8 and the Microsoft logo are registered trademarks of the Microsoft Corporation.

All other brand and product names are trademarks or registered trademarks of the companies and organisations in question.

更多信息 www.endress.com.cn/MS21