

Supply chain management software

SupplyCare Enterprise

Enterprise inventory management platform for transparent information within the supply chain



Benefits:

- Improves demand planning and lowers your inventories
- Enables business processes such as Vendor and Supplier Managed Inventory (VMI, SMI)
- Complete solution from inventory measurement and data acquisition to integration in your business processes
- Worldwide service and support network
- Faster reaction to supply chain volatilities
- Complete inventory visibility 24 hours a day, 7 days a week, anywhere within your enterprise, even on mobile devices

More information and current pricing:

www.fr.endress.com/SCE30B

Field of application: The SupplyCare inventory management platform supports users in collaborative demand planning, event-driven replenishment planning and scheduling as well as the reconciliation (in/out) and consolidation (totaling) of geographically distributed inventories. You can involve partners from all entities and even from different companies to make your supply chain smarter. The enterprise version is installed on your server infrastructure.

Features and specifications

Software**Measuring principle**

Inventory Management Solutions

Application Task

Data acquisition

Data management

Process monitoring & visualization

Field of Application

SupplyCare Enterprise SCE30B is a web-based operating program for the indication and monitoring of levels of e.g. tanks and silos spread all over the world.

Operating systems

Windows 10[®] (Enterprise)

Windows 11[®] (Enterprise)

Windows Server 2016 (Standard)

Windows Server 2019 (Standard)

Windows Server 2022 (Standard)

Processor type

4 cores, 3 GHz or better

Main memory

8 GB (free memory)

Hard-disk capacity

50 GB for full installation, depending on database size

Monitor resolution, display

1280 x 800 (Desktop), application can also be used on mobile devices

Interfaces

Business System via IMS Middleware

Web Browser

Software

Other

SupplyCare Enterprise runs by default in an Apache Tomcat-environment on an application server as service under Microsoft Windows. The operators and administrators operate the application via web browser from their desks.

Graphics: The minimum requirements do not take into account the requirements for the server operating system or other applications (e.g. antivirus software) installed on the server. The actual requirements and product functions can depend on the system configuration and the operating system. The requirements for the hardware will depend greatly on the desired number of users, failsafe performance etc..

Registered Trademarks

The following trademarks are either registered trademarks or trademarks of Microsoft Corporation in the United States and/ or other countries:

Microsoft®

Windows®

Windows Server®

The following trademarks are either registered trademarks or trademarks of Google LLC:

Google™

Google Chrome™

Google Maps™

The following trademarks are either registered trademarks or trademarks of Cisco Systems, Inc. and/ or its affiliates in the United States and certain other countries:

IOS®

Safari®, iPhone® and iPad® are trademarks of Apple® Inc., registered in the United States and other countries.

More information www.fr.endress.com/SCE30B