

# Proline Promag P 300

## Electromagnetic flowmeter

High-temperature flowmeter for process applications with a compact, easily accessible transmitter



More information and current pricing:

[www.apsc.endress.com/5P3B](http://www.apsc.endress.com/5P3B)

### Benefits:

- Diverse applications – wide variety of wetted materials
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

### Specs at a glance

- **Max. measurement error** Volume flow (standard):  $\pm 0.5\%$  o.r.  $\pm 1$  mm/s (0.04 in/s) Volume flow (option):  $\pm 0.2\%$  o.r.  $\pm 2$  mm/s (0.08 in/s)
- **Measuring range** 4 dm<sup>3</sup>/min to 9600 m<sup>3</sup>/h (1 gal/min to 44 000 gal/min)
- **Medium temperature range** Liner material PFA:  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F) Liner material PFA high-temperature:  $-20$  to  $+180$  °C ( $-4$  to  $+356$  °F) Liner material PTFE:  $-40$  to  $+130$  °C ( $-40$  to  $+266$  °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Liner: PFA; PTFE Electrodes: 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022); Tantalum; Platinum; Titanium

**Field of application:** Promag P is dedicated to chemical and process applications with corrosive liquids and highest medium temperatures. With its compact transmitter Promag P 300 offers a high flexibility in terms of operation and system integration: access from one side, remote

display and improved connectivity options. Heartbeat Technology ensures compliance and process safety at all times.

## Features and specifications

### Liquids

#### Measuring principle

Electromagnetic

#### Product headline

High-temperature flowmeter for process applications with a compact, easily accessible transmitter.

Dedicated to chemical and process applications with corrosive liquids and high medium temperatures.

#### Sensor features

Diverse applications – wide variety of wetted materials. Energy - saving flow measurement – no pressure loss due to cross section constriction.

Maintenance - free – no moving parts.

Nominal diameter: max. DN 600 (24"). All common Ex approvals.

#### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Liner made of PTFE or PFA. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

#### Nominal diameter range

DN 15 to 600 (½ to 24")

#### Wetted materials

Liner: PFA; PTFE

Electrodes: 1.4435 (F316L); Alloy C22, 2.4602 (UNS N06022);

Tantalum; Platinum; Titanium

## Liquids

### Measured variables

Volume flow, conductivity, mass flow

---

### Max. measurement error

Volume flow (standard):  $\pm 0.5\%$  o.r.  $\pm 1$  mm/s (0.04 in/s)

Volume flow (option):  $\pm 0.2\%$  o.r.  $\pm 2$  mm/s (0.08 in/s)

---

### Measuring range

4 dm<sup>3</sup>/min to 9600 m<sup>3</sup>/h (1 gal/min to 44 000 gal/min)

---

### Max. process pressure

PN 40, Class 300, 20K

---

### Medium temperature range

Liner material PFA:  $-20$  to  $+150$  °C ( $-4$  to  $+302$  °F)

Liner material PFA high-temperature:  $-20$  to  $+180$  °C ( $-4$  to  $+356$  °F)

Liner material PTFE:  $-40$  to  $+130$  °C ( $-40$  to  $+266$  °F)

---

### Ambient temperature range

Flange material carbon steel:  $-10$  to  $+60$  °C ( $+14$  to  $+140$  °F)

Flange material stainless steel:  $-40$  to  $+60$  °C ( $-40$  to  $+140$  °F)

---

### Sensor housing material

DN 15 to 300 ( $\frac{1}{2}$  to 12"): AlSi10Mg, coated

DN 350 to 600 (14 to 24"): Carbon steel with protective varnish

---

### Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

---

### Degree of protection

Standard: IP66/67, Type 4X enclosure

Option: IP69

---

### Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

## Liquids

### Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

### Inputs

Status input

4-20 mA input

### Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

### Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

### Hazardous area approvals

ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

### Product safety

CE, C-tick, EAC marking

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

## Liquids

### **Marine approvals and certificates**

LR approval, DNV GL approval, ABS approval, BV approval

---

### **Pressure approvals and certificates**

PED, CRN

---

### **Material certificates**

3.1 material

---

### **Hygienic approvals and certificates**

ACS, NSF 61

---

More information [www.apsc.endress.com/5P3B](http://www.apsc.endress.com/5P3B)