

# Proline Promag E 100 electromagnetic flowmeter

The economical flowmeter with an ultra-compact transmitter



More information and current pricing:

[www.apsc.endress.com/5E1B](http://www.apsc.endress.com/5E1B)

## Benefits:

- Cost-effective sensor – ideal solution for basic requirements
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Space-saving transmitter – full functionality on the smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification – Heartbeat Technology

## Specs at a glance

- **Max. measurement error** Volume flow (standard):  $\pm 0.5\%$  o.r.  $\pm 1$  mm/s (0.04 in/s) Volume flow (option):  $\pm 0.2\%$  o.r.  $\pm 2$  mm/s (0.08 in/s)
- **Measuring range** 4 dm<sup>3</sup>/min to 9600 m<sup>3</sup>/h (1 to 44 000 gal/min)
- **Medium temperature range** -10 to +110 °C (+14 to +230 °F)
- **Max. process pressure** PN 40, Class 150, 20K
- **Wetted materials** Liner: PTFE Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum

**Field of application:** The proven sensor for economical measurement of conductive liquids, Promag E, serves various basic applications in the chemical and process industry. Its ultra-compact transmitter delivers full performance on the smallest footprint and enables seamless system integration, making Promag E 100 the preferred choice for skid builders, equipment manufacturers and system integrators. Heartbeat Technology ensures compliance and process safety at all times.

---

## Features and specifications

---

### Liquids

**Measuring principle**

Electromagnetic

---

**Product headline**

The economical flowmeter with an ultra-compact transmitter.  
Fully suitable for basic applications in the chemical and process industry.

---

**Sensor features**

Cost-effective sensor – ideal solution for basic requirements. Energy - saving flow measurement – no pressure loss due to cross section constriction. Maintenance - free – no moving parts.

Nominal diameter: max. DN 600 (24"). Ex approvals for Zone 2. Liner made of PTFE.

---

**Transmitter features**

Space-saving transmitter – full functionality on the smallest footprint. Time-saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Local display available.

---

**Nominal diameter range**

DN 15 to 600 (½ to 24")

---

**Wetted materials**

Liner: PTFE

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum

---

**Measured variables**

Volume flow, conductivity, mass flow

---

**Max. measurement error**

Volume flow (standard):  $\pm 0.5$  % o.r.  $\pm 1$  mm/s (0.04 in/s)

Volume flow (option):  $\pm 0.2$  % o.r.  $\pm 2$  mm/s (0.08 in/s)

---

**Measuring range**

4 dm<sup>3</sup>/min to 9600 m<sup>3</sup>/h (1 to 44 000 gal/min)

---

---

## Liquids

**Max. process pressure**

PN 40, Class 150, 20K

---

**Medium temperature range**

-10 to +110 °C (+14 to +230 °F)

---

**Ambient temperature range**

-10 to +60 °C (+14 to +140 °F)

---

**Sensor housing material**

DN 15 to 300 (½ to 12"): AlSi10Mg, coated

DN 350 to 600 (14 to 24"): Carbon steel with protective varnish

---

**Transmitter housing material**

AlSi10Mg, coated

---

**Degree of protection**

IP67, type 4X enclosure

---

**Display/Operation**

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

---

**Inputs**

None

---

**Digital communication**

HART, PROFIBUS DP, Modbus RS485, EtherNet/IP, PROFINET

---

**Power supply**

DC 20 to 30 V

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, EAC

---

## Liquids

### Product safety

CE, C-Tick

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

### Pressure approvals and certificates

PED

---

### Material certificates

3.1 material

---

More information [www.apsc.endress.com/5E1B](http://www.apsc.endress.com/5E1B)