

# iTEMP TMT82 HART® 7 temperature transmitter

## Dual channel, SIL compliant temperature transmitter for use in hazardous areas



More information and current pricing:

[www.apsc.endress.com/TMT82](http://www.apsc.endress.com/TMT82)

### Benefits:

- Robust temperature transmitter delivering precise, long-term stable measurements for high plant availability
- SIL certification up to SIL2, SC3 according to IEC 61508:2010
- Versatile mounting and housing options: terminal head form B, DIN rail, field housing with separate terminal compartment, integrated display (**TID10**)
- Transmitter-sensor matching for highest measurement accuracy
- Sensor and hardware failure detection; diagnostic status information according to NAMUR NE 107
- Time-saving installation: Tool-free wiring with push-in terminal technology

### Specs at a glance

- **Accuracy** (Pt100)  $\leq 0,1K$  (digital) + 0,03% (set range)

**Field of application:** The iTEMP TMT82 is a highly reliable, accurate and long-term stable temperature transmitter for industrial processes requiring high availability. The versatile 2-channel device converts universal sensor inputs such as thermocouples or RTD into stable, scalable 4 to 20 mA output signals and **HART**® communication. With its built-in smart sensor monitoring capability and diagnostic status information according to NAMUR NE 107, the **SIL** 2, SC3 certified transmitter increases process safety and uptime.

### Features and specifications

**Temperature transmitters****Measuring principle**Head transmitter

---

**Input**2 x RTD, TC

---

**Output**1 x analog 4...20 mA / HART

---

**Auxiliary power supply**11...42 V DC

---

**Communication**HART-protocol

---

**Installation**Terminal head form B, DIN-Rail housing or field mount housing

---

**Accuracy**(Pt100)  $\leq 0,1K$  (digital) + 0,03% (set range)

---

**Galvanic isolation**yes

---

Temperature transmitters

**Certification**

Non-hazardous area

ATEX

CSA

FM

EAC

IECEX

NEPSI

FM+CSA

---

More information [www.apsc.endress.com/TMT82](http://www.apsc.endress.com/TMT82)