

Radiometric Interface measurement Source Container FQG63

Lightweight radiation source container with flexible extension element



More information and current pricing:

www.apsc.endress.com/FQG63

Benefits:

- Highest safety classification for the source supplied (DIN 25426/ISO 2919, typical classification C66646)
- Reliable measurement due to lightweight container and almost spherical design which provides optimized screening
- Flexible installation length up to 30m (98ft)
- Manually operated and padlock, cylinder lock or locking bolt for fixing the switching position
- Switch status easily identified
- Compact device that is easy to mount; adapter and centering flange for existing vessel flanges

Specs at a glance

- **Process temperature** max. 400°C (752°F) (diptube)
- **Process pressure absolute / max. overpressure limit** Any (diptube)
- **Main wetted parts** Non- contact

Field of application: The FQG63 source container is designed to hold the radioactive source during radiometric level, density and interface measurement. The radiation is damped in all directions as long as the source container is switched off. This guarantees highest safety for the personnel and a reliable measurement. If the source is switched on and lowered down into the process tank, it emits the radiation into all directions.

Features and specifications

Density**Measuring principle**Radiometric Density

Characteristic / Application

Source container with flexible extension element to position the source inside the process vessel (diptube)

Approximately 87 kg

Adapter flange: 10 kg

Ambient temperature

-52 °C...+200 °C

(-61 °F...+392 °F)

Process temperaturemax. 400°C (752°F) (diptube)

Process pressure absoluteAny

Wetted partsNon-contact

HygienicNon-contact

SpecialitiesControl area calculation with Applicator

Point Level / Liquids**Measuring principle**Radiometric Limit

Point Level / Liquids**Characteristic / Application**

Source container with flexible extension element to position the source inside the process vessel (diptube)

Approximately 87kg

Adapter flange: 10kg

Specialities

Control area calculation with Applicator

Ambient temperature

-52 °C...+200 °C
(-61 °F...+392 °F)

Process temperature

max. 400°C (752°F) (diptube)

Process pressure absolute / max. overpressure limit

Any (diptube)

Main wetted parts

Non- contact

Process connection

Non- contact

Continuous / Liquids**Measuring principle**

Radiometric

Characteristic / Application

Source container with flexible extension element to position the source inside the process vessel (diptube)

Approximately 87kg

Adapter flange: 10kg

Continuous / Liquids

Specialities

With flexible extension element

Ambient temperature

-52 °C...+200 °C
(-61 °F...+392 °F)

Process temperature

max. 400°C (752°F)

Process pressure absolute / max. overpressure limit

Any (diptube)

Main wetted parts

Non-contact

Process connection

Non-contact

Point Level / Solids

Measuring principle

Radiometric Limit

Characteristic / Application

Source container with flexible extension element to position the source inside the process vessel (diptube)

Approximately 87kg

Adapter flange: 10kg

Specialities

Control area calculation with Applicator

Ambient temperature

-52 °C...+200 °C
(-61 °F...+392 °F)

Point Level / Solids

Process temperature
max. 400°C (752°F)
(diptube)

Process pressure absolute / max. overpressure limit
Any (diptube)

Main wetted parts
Non- contact

Process connection
Non- contact

Process connection hygienic
Non- contact

Continuous / Solids

Measuring principle
Radiometric

Characteristic / Application

Source container with flexible extension element to position the source inside the process vessel (diptube)

Approximately 87kg

Adapter flange: 10kg

Specialities

Control area calculation with Applicator

Ambient temperature
-52 °C...+200 °C
(-61 °F...+392 °F)

Process temperature
max. 400°C (752°F)

Continuous / Solids

Process pressure absolute / max. overpressure limit

Any (diptube)

Main wetted parts

Non-contact

Process connection

Non-contact

More information www.apsc.endress.com/FQG63