

Dissolved oxygen transmitter Liquisys COM223

Compact panel device for water, wastewater, utilities and fish farming



More information and current pricing:

www.apsc.endress.com/COM223

Benefits:

- More operational safety: Continuous process check system, customized alarm configuration, calibration plausibility check.
- Reliable oxygen control: Current input for flow rate monitoring with controller shut off or for feedforward control.
- Easy to operate and service: Simple single-point calibration in air, air-saturated water or in the medium, direct access for manual contact control.
- Reduced maintenance: Automatic cleaning function (with Chemoclean) triggered by alarm or limit switch.
- Fit for every application: Numerous extensions, e.g. P(ID) controller, timer, etc., allow for flexible adaption to all processes.

Specs at a glance

- **Input** 1-channel transmitter
- **Output / communication** 0/4-20mA, Hart, Profibus.

Field of application: Liquisys COM223 is a standard transmitter for use with COS41 and COS61 oxygen sensors. It improves your operational safety thanks to continuous plausibility, process and sensor checks. Select from numerous hardware and software modules, such as relays or fieldbus communication, to adapt it exactly to your measuring task. This modularity also allows you to upgrade the transmitter at any time. A simple menu and calibration make configuration and operation fast and easy.

Features and specifications

Oxygen

Measuring principle

Amperometric oxygen measurement

Application

Water, waste water, process

Characteristic

4-wire transmitter with a two-line display

Design

Dissolved oxygen transmitter in a panel housing.

Material

Panel housing

Dimension

96mm x 96mm x 146mm(built in depth)

3.74x3.74x5.61inch(built in depth)

Temperature sensor

Display and current output

Connection

IP65

Input

1-channel transmitter

Output / communication

0/4-20mA, Hart, Profibus.

Additional certifications

CSA Gen. Purpose

More information www.apsc.endress.com/COM223