

Cell growth and biomass sensor OUSBT66

Hygienic NIR absorption measurement in fermentation and crystallization applications



More information and current pricing:

www.apsc.endress.com/OUSBT66

Benefits:

- Real-time measurement for optimized processes and product yields
- Reliable, precise measured values with excellent laboratory correlation
- Easy verification and calibration with NIST-traceable clip-on filters - no need for complex liquid calibrations
- Hygienic stainless steel body and sapphire windows without seals or crevices
- Suitable for CIP/SIP and autoclaving
- Various path lengths and sensor lengths for perfect fit into every fermenter and bioreactor
- PG 13.5 thread for standard assemblies or head plate installations

Specs at a glance

- **Measurement range** 0 to 4 AU 0 to 8 OD (depending on optical path length)
- **Process temperature** 0 to 90 °C (32 to 194 °F) Max. 135 °C for max. 2 hours
- **Process pressure** Max. 10 bar abs at 90 °C (Max. 150 psi at 194 °F)

Field of application: The OUSBT66 NIR absorption sensor monitors cell growth, biomass processes, algae systems and crystallization processes. It provides you with reliable, precise measured values in real-time to optimize your process and your product yield. The sensor's hygienic design is CIP/SIP resistant and allows autoclaving. Equipped with NIST-traceable and certified clip-on filters, OUSBT66 is outstandingly easy to calibrate and verify.

Features and specifications

Concentration

Measuring principle

Cell growth

Application

Cell growth and biomass in fermentation processes

Monitoring of algae concentration

Control of crystallization processes

Suspended solids measurement

Measurement range

0 to 4 AU

0 to 8 OD (depending on optical path length)

Design

Hygienic design:

Sterilizable and autoclaveable

Sapphire windows without seals and crevices

CIP/SIP resistant

Material

Sensor housing: Stainless Steel 1.4435 (316L)

Windows: Sapphire

O-ring: EPDM

Process temperature

0 to 90 °C (32 to 194 °F)

Max. 135 °C for max. 2 hours

Process pressure

Max. 10 bar abs at 90 °C

(Max. 150 psi at 194 °F)

Ingres protection

IP68

More information www.apsc.endress.com/OUSBT66