

Digital non-glass pH sensor Tophit CPS441D

Memosens ISFET electrode for the chemical, life sciences and food industries



More information and current pricing:

www.apsc.endress.com/CPS441D

Benefits:

- Unbreakable for highest product safety
- Resistant to poisoning thanks to constant refilling of KCl bridge electrolyte and separate reference lead
- Suitable for sterilization
- Low maintenance thanks to long calibration intervals
- Maximum process safety through non-contact inductive signal transmission
- Enables predictive maintenance due to storage of sensor and process-specific data
- Reduced operating costs due to minimized process downtime and extended sensor lifetime

Specs at a glance

- **Measurement range** pH 0-14
- **Process temperature** -15°C ... 135°C (5°F - 275°F)
- **Process pressure** max. 10bar/100°C (145 psi/212°F)

Field of application: Tophit CPS441D is the digital high performer for media with low conductivity or high organic solvents content. Designed for fast response, it accurately measures even in fast-changing medium compositions. Its unbreakable shaft ensures best safety of your products. Thanks to Memosens digital technology, CPS441D combines maximum process and data integrity with simple operation. It resists corrosion and moisture, enables lab calibration and facilitates predictive maintenance.

Features and specifications

pH

Measuring principle

ISFET

Application

- Special applications with high requirements with regard to accuracy and speed.- non-glass, break-proof- Low temperatures- Rapidly changing composition of media.- highly clogging media.- Low conductivities

Characteristic

Ion sensitive field effect transistor (Isfet)-Technology.- Overhead installation- rapid response at low temperature.- lower amount of maintenance required than with glass.- 3A

Measurement range

pH 0-14

Measuring principle

- Ceramic diaphragm.- Liquid lead

Design

All shaft lengths with temperature sensor

Material

Peek / metal oxide / Ceramic / EPDM

Dimension

Diameter : 12mm (0.47 inch) Shaft length : 120,225,360,425mm
(4.72/8.86/14.2/16.7 inch)

Process temperature

-15°C ... 135°C
(5°F - 275°F)

Process pressure

max. 10bar/100°C (145 psi/212°F)

Temperature sensor

Optional with integrated Pt1000

pH

Ex certification

ATEX

FM

Connection

Contactless, inductive, digitale connection head with Memosens-Technology

Ingres protection

IP68

More information www.apsc.endress.com/CPS441D