

# Proline Promass K 10 Coriolis flowmeter

Flowmeter with minimized total cost of ownership with easy-to-use operation concept



More information and current pricing:

[www.apsc.endress.com/8KBB](http://www.apsc.endress.com/8KBB)

## Benefits:

- Cost-effective general-purpose device – alternative to mechanical flowmeters
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in-/outlet run needs
- Optimum usability – operation with mobile devices and SmartBlue app or display with touch screen
- Simple, time-saving commissioning – guided parameterization in advance and in the field
- Integrated verification – Heartbeat Technology

## Specs at a glance

- **Max. measurement error** Mass flow (liquid):  $\pm 0.5\%$  (standard),  $\pm 0.15\%$  (option) Mass flow (gas):  $\pm 1\%$
- **Measuring range** 0 to 180 000 kg/h (0 to 6615 lb/min)
- **Medium temperature range**  $-40$  to  $+150\text{ }^{\circ}\text{C}$  ( $-40$  to  $+302\text{ }^{\circ}\text{F}$ )
- **Max. process pressure** PN 40, Class 300, 40K
- **Wetted materials** Measuring tube: 1.4539 (904L) Connection: 1.4404 (316/316L)

**Field of application:** Promass K is the cost-efficient Coriolis solution for elementary mass flow measuring tasks. It provides dependable measurement in basic applications featuring air, gas, fuel and water. With its straightforward hard- and software design, Promass K 10 simplifies every step in its life cycle from engineering to servicing at usual Endress+Hauser quality. Heartbeat Technology ensures measurement reliability and enables extension of recalibration cycles.

---

## Features and specifications

---

Gas

**Measuring principle**

Coriolis

---

**Nominal diameter range**

DN 8 to 80 ( $\frac{3}{8}$  to 3")

---

**Wetted materials**

Measuring tube: 1.4539 (904L)

Connection: 1.4404 (316/316L)

---

**Measured variables**

Mass flow, temperature, Density (option), volume flow, corrected volume flow

---

**Max. measurement error**

Mass flow (liquid):  $\pm 0.5$  % (standard),  $\pm 0.15$  % (option)

Mass flow (gas):  $\pm 1$  %

---

**Measuring range**

0 to 180 000 kg/h (0 to 6615 lb/min)

---

**Max. process pressure**

PN 40, Class 300, 40K

---

**Medium temperature range**

-40 to +150 °C (-40 to +302 °F)

---

**Ambient temperature range**

Standard: -20 to +60 °C (-4 to +140 °F)

---

**Sensor housing material**

Stainless steel 1.4301 (304)

---

**Transmitter housing material**

AlSi10Mg, coated

---

## Gas

**Degree of protection**

Standard: IP66/67, Type 4X enclosure

---

**Display/Operation**

2.4" LCD display with touch & auto rotate; Configuration and operation via SmartBlue App (Bluetooth) possible

---

**Outputs**

4-20 mA HART (active/passive), Pulse/frequency/switch output  
Modbus RS485, 4-20 mA

---

**Digital communication**

HART, MODBUS RS485

---

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

**Hazardous area approvals**

ATEX

IECEX

cCSAus

EAC

NEPSI

INMETRO

JPN

Uk Ex

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

CRN, PED

---

---

**Gas****Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

EC 1935, FDA, GB4806, cGMP

---

**Liquids****Measuring principle**

Coriolis

---

**Product headline**

Flowmeter with minimized total cost of ownership with easy-to-use operation concept.

Measurement of liquids and gases in utility processes and basic applications.

---

**Sensor features**

Cost-effective general-purpose device – alternative to mechanical flowmeters. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Compact dual-tube sensor. Medium temperature up to +150 °C (+302 °F). Process pressure up to 100 bar (1450 psi).

---

**Transmitter features**

Optimum usability – operation with mobile devices and SmartBlue app or display with touch screen. Simple, time-saving commissioning – guided parameterization in advance and in the field. Integrated verification – Heartbeat Technology.

System integration with HART, Modbus RS485. Flexible operation with app and optional display.

---

**Nominal diameter range**

DN 8 to 80 ( $\frac{3}{8}$  to 3")

---

**Wetted materials**

Measuring tube: 1.4539 (904L)

Connection: 1.4404 (316/316L)

---

---

## Liquids

---

### Measured variables

Mass flow, temperature, Density (option), volume flow, corrected volume flow

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.5$  % (standard),  $\pm 0.15$  % (option)  
Mass flow (gas):  $\pm 1$  %

---

### Measuring range

0 to 180 000 kg/h (0 to 6615 lb/min)

---

### Max. process pressure

PN 40, Class 300, 40K

---

### Medium temperature range

-40 to +150 °C (-40 to +302 °F)

---

### Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

---

### Sensor housing material

Stainless steel 1.4301 (304)

---

### Transmitter housing material

AlSi10Mg, coated

---

### Degree of protection

Standard: IP66/67, Type 4X enclosure

---

### Display/Operation

2.4" LCD display with touch & auto rotate; Configuration and operation via SmartBlue App (Bluetooth) possible

---

### Outputs

4-20 mA HART (active/passive), Pulse/frequency/switch output  
Modbus RS485, 4-20 mA

---

### Digital communication

HART, MODBUS RS485

---

## Liquids

---

### Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

### Hazardous area approvals

ATEX

IECEX

cCSAus

EAC

NEPSI

INMETRO

JPN

UK Ex

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

### Pressure approvals and certificates

CRN, PED

---

### Material certificates

3.1 material

---

### Hygienic approvals and certificates

EC 1935, FDA, GB4806, cGMP

---

More information [www.apsc.endress.com/8KBB](http://www.apsc.endress.com/8KBB)