

Deltatop DO69S



More information and current pricing:

www.apsc.endress.com/DO69S

Benefits:

- Customized or application-specific flowmeter systems based on the differential pressure method for special applications
- Optimized for minimum pressure loss, maximum accuracy or maximum turndown
- Measuring range of the Deltabar differential pressure transmitter adjusted on delivery
- Based on international standards (e.g. ISO 5167)
- Cost-effective solution thanks to its robust design without moving parts

Specs at a glance

- **Max. measurement error** typically < 1,5% of calculated volume or mass acc. ISO5167 without calibration. Uncertainty of primary element excluding uncertainty of density or compensation."
- **Measuring range** 0.4 ... 600'000 m³/h
- **Medium temperature range** Compact version: -200°C ... 200°C -328°F ... 392°F Remote version: -200°C ... 1000°C -328°F ... 1832°F
- **Max. process pressure** PN2,5 ... 400 Cl.150 ... 4500

Field of application: The Deltatop DO69S is part of the universal differential pressure flowmeter systems. With venturi tubes, nozzles, orifice plates and Deltabar differential pressure transmitters. In addition to the standard products DO61W, DO62C, DO63C, DO64P, DO65F, Endress+Hauser also supplies primary devices in the form of orifice plates in a wide range of special designs which cannot be specified within the framework of the standard products mentioned above.

Features and specifications

Liquids

Measuring principle

Liquids

Product headline

Calculated volume or mass flow measurement. dp primary element (orifice).

Special designs.

Sensor features

Internationally standardized.

Nominal pipe size DN10...2000 ; 3/8...80".

Meter runs.

Weld-In versions.

Compact or remote design.

Optimizable for minimized pressure loss, improved uncertainty or maximized Turndown.

Deltabar S/M differential pressure transmitter.

Nominal diameter range

DN 10...2000

3/8" ... 80"

Max. measurement error

typically < 1% of calculated volume or mass acc. ISO5167 without calibration.

Measuring range

0.02 ... 70'000m³/h

Max. process pressure

PN2,5 ... 400

Cl.150 ... 4500

Medium temperature range

Compact version:

-200°C ... 200°C

-328°F ... 392°F

Remote version:

-200°C ... 1000°C

-328°F ... 1832°F

Liquids**Degree of protection**

Transmitter (Deltabar):

IP67

NEMA6P

Display/Operation

Transmitter (Deltabar):

4-line display

3 push buttons

Quick setup

HistoROM

Outputs

Transmitter (Deltabar):

4 ... 20 mA

Digital communication

Transmitter (Deltabar):

HART

PROFIBUS PA

FOUNDATION Fieldbus

Hazardous area approvals

Transmitter (Deltabar):

ATEX

FM

CSA

IEC

TIIS

NEPSI

Steam**Measuring principle**

Steam**Product headline**

Calculated volume or mass flow measurement. dp primary element (orifice).

Special designs.

Sensor features

Internationally standardized.

Nominal pipe size DN10...2000 ; 3/8...80".

Meter runs.

Weld-In versions.

Compact or remote design.

Optimizable for minimized pressure loss, improved uncertainty or maximized Turndown.

Deltabar S/M differential pressure transmitter.

Nominal diameter range

DN 10...2000

3/8" ... 80"

Max. measurement error

typically < 1% of calculated volume or mass acc. ISO5167 without calibration.

Uncertainty of primary element excluding uncertainty of density or compensation.

Measuring range

0.4 ... 600'000 m³/h

2.0 kg/h ... 3'000 t/h at 10bar/230°C

Max. process pressure

PN2,5 ... 400

Cl.150 ... 4500

Steam**Medium temperature range**

Compact version:

-200°C ... 200°C

-328°F ... 392°F

Remote version:

-200°C ... 1000°C

-328°F ... 1832°F

Degree of protection

Transmitter (Deltabar):

IP67

NEMA6P

Display/Operation

Transmitter (Deltabar):

4-line display

3 push buttons

Quick setup

HistoROM

Outputs

Transmitter (Deltabar):

4 ... 20 mA

Digital communication

Transmitter (Deltabar):

HART

PROFIBUS PA

FOUNDATION Fieldbus

Hazardous area approvals

Transmitter (Deltabar):

ATEX

FM

CSA

IEC

TIIS

NEPSI

Steam

Gas

Measuring principle

Product headline

Calculated volume or mass flow measurement. dp primary element (orifice).
Special designs.

Sensor features

Internationally standardized.
Nominal pipe size DN10...2000 ; 3/8...80".
Meter runs.
Weld-In versions.
Compact or remote design.
Optimizable for minimized pressure loss, improved uncertainty or maximized Turndown.
Deltabar S/M differential pressure transmitter.

Nominal diameter range

DN 10...2000
3/8" ... 80"

Max. measurement error

typically < 1,5% of calculated volume or mass acc. ISO5167 without calibration.
Uncertainty of primary element excluding uncertainty of density or compensation."

Measuring range

0.4 ... 600'000 m³/h

Max. process pressure

PN2,5 ... 400
Cl.150 ... 4500

Gas

Medium temperature range

Compact version:

-200°C ... 200°C

-328°F ... 392°F

Remote version:

-200°C ... 1000°C

-328°F ... 1832°F

Degree of protection

Transmitter (Deltabar):

IP67

NEMA6P

Display/Operation

Transmitter (Deltabar):

4-line display

3 push buttons

Quick setup

HistoROM

Outputs

Transmitter (Deltabar):

4 ... 20 mA

Digital communication

Transmitter (Deltabar):

HART

PROFIBUS PA

FOUNDATION Fieldbus

Hazardous area approvals

Transmitter (Deltabar):

ATEX

FM

CSA

IEC

TIIS

NEPSI

Gas

More information www.apsc.endress.com/D069S