

Absolute and gauge pressure Cerabar PMP71

Digital pressure transmitter with welded metal sensor for measurement in gases, steam or liquids



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/PMP71

Lợi ích:

- Best accuracy, reproducibility and long-term stability
- Highest safety due to gas tight feedthrough with capabilities up to SIL2/3, certified to IEC 61508
- Easy menu-guided commissioning via local display, 4 to 20mA with HART, PROFIBUS PA, FOUNDATION Fieldbus
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Overload-resistant and function-monitored from the measuring cell to the electronics
- Available with mounted manifolds: always fit, always tested for leaks
- Seamless and independent system integration (HART/PA/FF)

Tổng quan về thông số kỹ thuật

- **Accuracy** 0,075% "PLATINUM" 0,05%
- **Process temperature** -40°C...125°C (-40°F...257°F)
- **Pressure measuring range** 100mbar...700bar (1.5psi...10.500psi)
- **Main wetted parts** Alloy C276 316L Rhodium
- **Material process membrane** 316L, AlloyC, Rhodium > Gold

Phạm vi ứng dụng: The Cerabar PMP71 digital pressure transmitter with metallic membrane is typically used in process applications for pressure, level, volume or mass measurement in liquids or gases. PMP71 is designed for high pressure applications up to 700bar. Quick Setup with freely adjustable measuring range without pressure specification. Designed according to IEC 61508 for use in SIL2/3 safety systems and

available with MID Parts Certificate suitable for custody transfer applications.

Tín năng và thông số kỹ thuật

Pressure

Measuring principle

Absolute and gauge pressure

Characteristic

Digital transmitter with piezoresistive sensor and welded metallic membrane

Modular transmitter

Long term stability

Enhanced safety via self diagnostic functions Secondary process barrier

Supply voltage

4...20 mA HART

10,5...45V DC (Non Ex):

Ex ia: 10,5...30V DC

PROFIBUS PA:

9...32 V DC (Non Ex)

FOUNDATION Fieldbus:

9...32 V DC (Non Ex)

Reference Accuracy

Standard: 0.05%

Platinum: up to 0.025%

Pressure**Long term stability**

0.05 % of URL/ year

0.07 % of URL/ 5 years

0.1 % of URL/ 10 years

Process temperature

-40°C...125°C

(-40°F...257°F)

Ambient temperature

-50°C...85°C

(-58°F...185°F)

Measuring cell

100 mbar...700 bar

(1.5 psi...10.500 psi)

relative/ absolute

Smallest calibratable span

5 mbar (0.075 psi)

Vacuum resistance

10 mbar (0.15 psi)

Max. Turn down

100:1

Max. overpressure limit

1050 bar (15.750 psi)

Pressure**Process connection**

Thread:

G1/2...G2, R1/2, MNPT1/2...MNPT2, R1/2

Flange:

DN25...DN80,

ASME 1"...4",

JIS 10K...20K

Material process membrane

316L, AlloyC,

Rhodium > Gold

Material gasket

None, measuring cell welded

Fill fluid

Silicone oil,

Inert oil

Material housing

Die-cast aluminum,

AISI 316L

Pressure**Communication**

4...20 mA HART

1- 5V DC Low Power

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, EAC

Safety approvals

SIL

Design approvals

EN10204-3.1

NACE MR0175

Marine approvals

GL/ABS

Drinking water approvals

NSF

Specialities

Diagnostic functions

Successor

PMP71B

Continuous / Liquids**Measuring principle**

Absolute and gauge pressure

Continuous / Liquids**Characteristic / Application**

Digital transmitter with piezoresistive sensor and welded metallic membrane

Modular transmitter

Long term stability

Enhanced safety via self diagnostic functions

Secondary process barrier

Specialities

diagnostic functionalities

different languages in software

Supply / Communication

4...20mA HART:

10,5...45V DC

Ex ia: 10,5...30V DC

PROFIBUS PA /

FOUNDATION Fieldbus:

9...32V DC

Accuracy

0,075%

"PLATINUM" 0,05%

Long term stability

0,05% of URL/year

Ambient temperature

-50°C...85°C

(-58°F...185°F)

Process temperature

-40°C...125°C

(-40°F...257°F)

Process pressure absolute / max. overpressure limit

1050bar (15,750psi)

Continuous / Liquids**Pressure measuring range**

100mbar...700bar
(1.5psi...10.500psi)

Main wetted parts

Alloy C276
316L
Rhodium

Process connection

Threads
Flanges (DIN, ASME, ...) with flush membrane

Max. measurement distance

7000m (22.966ft) H₂O

Communication

4...20 mA HART

1- 5V DC Low Power

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, EAC

Safety approvals

SIL

Design approvals

EN 10204-3.1

NACE MR0175, MR0103

Marine approval

GL/ ABS

Continuous / Liquids**Drinking water approvals**

NSF

Options

HistoROM/M-Dat

4-line digital display

SS- or Aluminiumhousing

Separate housing

Successor

PMP71B

Application limitsMeasuring cell: Metal
weldedIf pressurized, possibly
use differential pressure
meas-urement with two
pressure transmitters
(electronic dp). Observe
ratio head pressure :
hydrostatic pressure

Thông tin bổ sung www.apsc.endress.com/PMP71