

# Capacitance Point level detection Solicap FTI56

## Point level detection for fine-grained to coarse-grained bulk solids



### Lợi ích:

- Extremely robust design for harsh process conditions
- Cost savings thanks to easy and fast commissioning as calibration is performed at the press of a button
- Universal application thanks to wide range of certificates and approvals
- Two-stage overvoltage protection against static discharges from the silo
- Increased safety due to permanent automatic monitoring of electronics
- Reduction in storage costs thanks to easy-to-shorten rod model (for partial insulation) and rope model (for partial and full insulation)

### Tổng quan về thông số kỹ thuật

- **Process temperature** -50°C ... 180°C (-58°F ... 356°F)
- **Process pressure absolute / max. overpressure limit** Vacuum ... 25 bar (Vacuum ... 362 psi)

Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/FTI56](http://www.apsc.endress.com/FTI56)

**Phạm vi ứng dụng:** Solicap FTI56 is a fully/partly insulated and robust rope probe for point level detection of fine-grained to coarse-grained bulk solids. It offers maximum reliability and is suited for a wide range of applications thanks to numerous certificates and approvals. Due to its robust construction, it can also be used to provide accurate measurements in applications with very high tensile loads up to 60kN.

### Tín năng và thông số kỹ thuật

---

**Point Level / Solids****Measuring principle**Capacitive Solid

---

**Characteristic / Application**

Fully / partly insulated rope probe for small-grain / large-grain solids

Simple calibration

Suitable for abrasive media

Very robust probe

---

**Specialities**

Inactive length

High tensile loading

Extremely robust probe

---

**Supply / Communication**

19 ... 253V AC

10 ... 55V DC-PNP

19...253V AC bzw 10...55V DC

8/16mA, 11 ... 36V DC

PFM

3-wire

---

**Ambient temperature**

-50°C ... 70°C

(-58°F ... 158°F)

---

**Process temperature**

-50°C ... 180°C

(-58°F ... 356°F)

---

**Process pressure absolute / max. overpressure limit**

Vacuum ... 25 bar

(Vacuum ... 362 psi)

---

**Main wetted parts**PTFE, PA, 316L, Steel

---

---

**Point Level / Solids****Max. tensile strength**

60 kN

---

**Process connection**

Thread R1 1/2, NPT1 1/2

Flanges from DN50.../ASME 2".../JIS...

---

**Sensor length**

0.5m ... 22m

(1.6ft ... 72ft)

Inactive length: 0.1m....1m

(3"...39")

---

**Communication**

2- wire 19-253 VAC

DC PNP

Relais DPDT

PFM

3-wire

8/16 mA

---

**Certificates / Approvals**

ATEX, FM, CSA, IEC Ex, JPN Ex, NEPSI

---

**Safety approvals**

SIL

---

**Components**

PFM: FTC325, FTC625, FTC470Z, FTC471Z

3-wire: FTC325

---

**Application limits**

DK min 2

---

Thông tin bổ sung [www.apsc.endress.com/FTI56](http://www.apsc.endress.com/FTI56)