

Raman calibration accessory

Fast, simple, and accurate wavelength and intensity calibration for Raman analyzers



More information and current pricing:

www.apsc.endress.com/KHCA1

Benefits:

- Robust calibration protocol
- Excellent system accuracy
- Unparalleled instrument precision
- Facilitates easy calibration transfer with minimal technical support required
- White Light NIST Traceable
- Compatible with Cyclohexane ASTM
- Chemical models instrument-independent

Specs at a glance

- **Sampling probe compatibility** Raman Rxn-10 (with accessory optics) Raman Rxn-20 (with accessory optics) Raman Rxn-40 Raman Rxn-41 Raman Rxn-45

Field of application: Unlike many Raman instruments, Endress+Hauser Raman analyzers are powered by Kaiser Raman technology and utilize calibration protocols to ensure both wavelength and intensity accuracy and precision. The Raman calibration accessory offers an easy-to-use calibration protocol that provides accuracy and repeatability critical for qualitative and quantitative Raman analysis. Used routinely, this protocol facilitates calibration transfer between laboratory instruments and on-line process analyzers.

Features and specifications

Measuring principle

Raman spectroscopy

Unit dimensions (width x height x depth in mm)

Control unit: 12 x 270 x 43

Lamp head: 50 x 80 x 19

Weight (kg)

Control Unit: 1.60

Lamp head: 0.10

Sampling probe compatibility

Raman Rxn-10 (with accessory optics)

Raman Rxn-20 (with accessory optics)

Raman Rxn-40

Raman Rxn-41

Raman Rxn-45

Spectral intensity referenceTungsten-halogen

Spectral intensity calibration range

HCA-532: 534.5 to 694.0 nm

HCA-785: 790.7 to 1074.5 nm

HCA-1000: 1012.6 to 1304.6 nm

Spectral intensity output repeatability (over any 4000 cm⁻¹ spectrum)

Short Term: 2%

Over 100 hours: 2.65%

Adapter options

Lamp Housing Adapters for sampling optics (NCO 0.4", 0.5", 2.5", 3" options)

Immersion (IO) 1/2", 1/4" adapter

bIO adapter (12 mm)

Fiber Adapters: FC and SMA

Electrical data

Power Source: 100–240 VAC 50/60 Hz

Power Consumption: 22 W Maximum

CE Certified: Yes

More information www.apsc.endress.com/KHCA1