

iTEMP TMT121

DIN rail temperature transmitter

Transformation of sensor signals into stable and standardized output signals for all industries



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/TMT121

Lợi ích:

- High accuracy in total ambient temperature range
- Fault signal on sensor break or short circuit, NAMUR NE 43 compliant
- Safe operation in hazardous areas - International approvals such as ATEX Ex ia, NEPSI, FM IS, CSA IS
- EMC to NAMUR NE 21, CE
- Online configuration during measurement
- Galvanic isolation
- Output simulation

Tổng quan về thông số kỹ thuật

- **Accuracy** (Pt100, -50...200 °C) $\leq 0,2$ K (Pt100, -58...392 °F) $\leq 0,4$ °F

Phạm vi ứng dụng: Unsurpassed reliability, accuracy and long-term stability in critical processes over all industries. The configurable transmitter not only transfers converted signals from resistance thermometers (RTD) and thermocouples (TC), it also transfers resistance and voltage signals. The standardized output signal is a 4 to 20 mA signal. Swift and easy operation, visualization and maintenance by PC using operating software. Installation is realized on DIN rail as per IEC 60715 (housing width: 22.5 mm)

Tín năng và thông số kỹ thuật

Temperature transmitters**Measuring principle**Rail transmitter

Input1 x RTD, TC, Ohm, mV

Output1 x analog 4...20 mA

Auxiliary power supply

12...35 V DC (standard-version)

12...30 V DC (Ex-version)

CommunicationPCP (pc-programmable)

InstallationDIN rail

Accuracy(Pt100, -50...200 °C) $\leq 0,2$ K(Pt100, -58...392 °F) $\leq 0,4$ °F

Galvanic isolationyes

Temperature transmitters

Certification

UL rec. Comp

marine approval

GOST Metrology

FM IS,NI,Class I,Div.1+2,Group ABCD

CSA IS,NI,Class I,Div.1+2,Group ABCD

ATEX II2(1)G Ex ia[ia Ga] IIC T6 Gb

ATEX II3G Ex nA IIC T6

FM+CSA IS,NI,Class I,Div.1+2,Group
ABCD

CSA General Purpose

NEPSI Ex ia IIC T4-T6

NEPSI Ex nA II T4-T6

Thông tin bổ sung www.apsc.endress.com/TMT121