

# Radar measurement Time-of-Flight Micropilot FMR54

For level measurement in liquids where strong steam or ammonia can occur



## Lợi ích:

- Hardware and software developed according to IEC 61508 up to SIL3 (in homogeneous redundancy)
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even in the presence of obstructions in the vessel due to new Multi-Echo Tracking evaluation
- Reliable measurement even for changing product and process conditions
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test concept for SIL and WHG saves time and cost

Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/FMR54](http://www.apsc.endress.com/FMR54)

## Tổng quan về thông số kỹ thuật

- **Accuracy** +/- 6 mm (0.24 in)
- **Process temperature** -60...+400°C (-76...+752°F)
- **Process pressure absolute / max. overpressure limit**  
Vacuum...160 bar (Vacuum...2320 psi)
- **Max. measurement distance** Max. measurement distance
- **Main wetted parts** 316L

**Phạm vi ứng dụng:** Micropilot FMR54 is prepared for the use in high temperature and high pressure applications and with the specially designed planar antenna it is particularly suited for stilling well applications. The FMR54 free space radar is used for continuous, non-

contact level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or vapors.

## Tín năng và thông số kỹ thuật

### Continuous / Liquids

#### Measuring principle

Level radar

#### Characteristic / Application

Continuous non-contact level measurement for use in high-pressure and high-temperature applications,

Horn or planar antenna

#### Specialities

Heartbeat Technology,

SIL 2 according to IEC 61508,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

Safety and reliability with Multi-Echo Tracking,

HistoROM,

RFID TAG for easy identification

#### Supply / Communication

2-wire (HART / PROFIBUS PA/ FOUNDATION Fieldbus)

4-wire (HART)

Bluetooth® wireless technology and App (optional)

## Continuous / Liquids

**Frequency**

C-band (~6 GHz)

**Accuracy**

+/- 6 mm (0.24 in)

**Ambient temperature**

-50...+80 °C

(-58...+176 °F)

**Process temperature**

-60...+400°C

(-76...+752°F)

**Process pressure absolute / max. overpressure limit**

Vacuum...160 bar

(Vacuum...2320 psi)

**Main wetted parts**

316L

**Process connection**

Flange:

DN80...DN300,

ASME 3"...12",

JIS 10K, 20K

**Application**

Application

**Max. measurement distance**

Max. measurement distance

---

**Continuous / Liquids****Communication**

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Bluetooth® wireless technology

---

**Certificates / Approvals**

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC

---

**Safety approvals**

Overfill protection WHG

SIL

---

**Design approvals**

EN 10204-3.1

NACE MR0175, MR0103

ASME B31.3

AD2000

---

**Marine approval**

GL/ ABS/ LR/ BV/ DNV

## Continuous / Liquids

### Options

Display,

Customized parameterization,

Remote operation via SmartBlue App using Bluetooth<sup>®</sup>,

PWIS free,

Gastight feed through

---

### Application limits

Application limits

---

Thông tin bổ sung [www.apsc.endress.com/FMR54](http://www.apsc.endress.com/FMR54)