

Hydrostatic Level measurement Deltapilot FMB70

Highest performance pressure sensor with the Contite cell for hydrostatic level measurement



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/FMB70

Lợi ích:

- Hermetically sealed Contite measuring cell with condensate-resistance, high reference accuracy: $\pm 0.1\%$, optionally $\pm 0.075\%$ and minimum temperature effects thanks to active temperature compensation
- Best batch-to-batch repeatability and long-term stability
- Modular concept for easy replacement of display or electronics
- HistoROM/M-DAT data backup for instrument settings and measured values
- Function-monitored from the measuring cell to the electronics
- Seamless and independent system integration (HART/PA/FF)
- International usage thanks to a wide range of approvals

Tổng quan về thông số kỹ thuật

- **Accuracy** Standard 0.1% Optional 0.075%
- **Process temperature** $-10^{\circ}\text{C} \dots +100^{\circ}\text{C}$ ($+14^{\circ}\text{F} \dots +212^{\circ}\text{F}$)
- **Pressure measuring range** 100 mbar...10 bar (1.5 psi...150 psi)
- **Process pressure absolute / max. overpressure limit** 40 bar (600 psi)
- **Main wetted parts** Alloy C 316L

Phạm vi ứng dụng: The Deltapilot FMB70 with the condensate resistant Contite measuring cell and two-chamber housing is typically used in the process and hygienic applications. It is made for level measurement in liquid and paste-like media in open or closed containers and unaffected by possible foam formation. The integrated HistoROM/M-DAT data module makes management of process and device parameters easy. Designed according to IEC 61508 for use in SIL3 safety systems.

Tín năng và thông số kỹ thuật

Pressure

Measuring principle

Hydrostatic pressure

Characteristic

Pressure transmitter for hydrostatic level measurement with flush mounted metallic Contite measuring cell:
Hermetically sealed, condensate-resistant, climatic-proofed and with lowest temperature influences
Compact version

Supply voltage

4...20 mA HART
10,5...45 VDC (Non Ex):
Ex ia: 10,5...30 VDC
PROFIBUS PA:
9...32 VDC (Non Ex)
FOUNDATION Fieldbus:
9...32 VDC (Non Ex)

Reference Accuracy

Standard 0.1%
Optional 0.075%

Long term stability

0.05 % of URL/year

Process temperature

-10°C...100°C
(14°F...212°F)

Ambient temperature

-40°C...85°C
(-40°F...185°F)

Pressure

Measuring cell

100 mbar...10 bar
(1.5 psi...150 psi)

Smallest calibratable span

25 mbar (3.63 psi)

Vacuum resistance

0 mbar abs.

Max. overpressure limit

40 bar (600 psi)

Process connection

Thread:

G1 1/2, MNPT1/2

Flange:

DN40...DN100,

ASME 1 1/2"...4",

JIS 10K

Process connection hygienic

Tri-Clamp

DIN11851

DIN11864-1

NEUMO

Varivent N

SMS

DRD

Material process membrane

316L, AlloyC,

Gold-Rhodium

Material gasket

None, measuring cell welded

Pressure**Fill fluid**

Inert oil,
Synthetic oil

Material housing

316L, Die-cast aluminum

Communication

4 ... 20 mA HART
PROFIBUS PA
FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, INMETRO, NEPSI, EAC

Safety approvals

SIL

Design approvals

EN10204-3.1
NACE MR0175
MR0103

Hygienic approvals

3A, EHEDG
CoC ASME-BPE

Marine approvals

GL, DNV

Drinking water approvals

NSF

Specialities

Gold-rhodium coated membrane

Continuous / Liquids**Measuring principle**

Hydrostatic

Characteristic / Application

Compact pressure transmitter for hydrostatic level measurement with flush mounted metallic Contite measuring cell:
Hermetically sealed, condensate-resistant and climatic-proofed

Specialities

Diagnostic functions

Supply / Communication

4...20mA HART:
10,5...45V DC
Ex ia: 10,5...30V DC
PROFIBUS PA /
FOUNDATION Fieldbus:
9...32V DC (Non Ex)

Accuracy

Standard 0.1%
Optional 0.075%

Long term stability

0.05 % of URL/year

Ambient temperature

-40°C...+85°C
(-40°F...+185°F)

Process temperature

-10°C...+100°C
(+14°F...+212°F)

Process pressure absolute / max. overpressure limit40 bar (600 psi)

Continuous / Liquids**Pressure measuring range**

100 mbar...10 bar
(1.5 psi...150 psi)

Main wetted parts

Alloy C
316L

Process connection

Thread:
G1 1/2, MNPT1/2
Flange:
DN40...DN100,
ASME 1 1/2"...4",
JIS 10K

Process connection hygienic

Tri-Clamp
DIN11851
DIN11864-1
NEUMO
Varivent N
SMS
DRD

Max. measurement distance

100 m (328 ft) H₂O

Communication

4...20 mA HART
PROFIBUS PA
FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, INMETRO, NEPSI, EAC

Safety approvals

SIL

Continuous / Liquids**Design approvals**

EN10204-3.1

NACE MR0175, MR0103

Hygienic approvals

3A, EHEDG

CoC ASME-BPE

Marine approval

GL/ DNV

Drinking water approvals

NSF

Options

HistoROM/M-Dat

4-line digital display

SS- or Aluminiumhousing

Separate housing

Application limits

Measuring cell: Contite,
condensate-proof, watertight,
metal welded

If pressurized, possibly use
differential pressure measurement
with two pressure
transmitters. Observe ratio
head pressure : hydrostatic
pressure

Thông tin bổ sung www.apsc.endress.com/FMB70