

# Radiometric level and density measurement Gamma Source FSG61

Gamma radiation source ( $^{60}\text{Co}$ ) for radiometric level, point level, density and interface measurement



## Lợi ích:

- Specially constructed source capsule conforms to strictest safety requirements:  
Typically class C66646 to ISO 2919
- Point source in special source container ensures simple handling and easy installation
- Choice of activity ensures optimized dosage for your application
- High penetration energy even for extreme applications

## Tổng quan về thông số kỹ thuật

- **Process temperature** Any
- **Process pressure / max. overpressure limit** Any

Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/FSG61](http://www.apsc.endress.com/FSG61)

**Phạm vi ứng dụng:** The Gamma Source FSG61 is specially suited for level applications with thick tank walls, high pressure or for density applications with big pipe diameters and large density ranges thanks to its high penetration energy.

## Tín năng và thông số kỹ thuật

Continuous / Liquids

**Measuring principle**

Radiometric

**Continuous / Liquids****Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

**Process temperature**

Any

**Process pressure / max. overpressure  
limit**

Any

**Components**

Installed in source container

**Continuous / Solids****Measuring principle**

Radiometric

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

---

**Continuous / Solids****Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

Activity calculation with  
Applicator

---

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

---

**Process temperature**

Any

---

**Process pressure / max. overpressure  
limit**

Any

---

**Components**

Installed in source container

---

**Point Level / Liquids****Measuring principle**

Radiometric Limit

---

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

Activity calculation with  
Applicator

---

**Point Level / Liquids****Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

---

**Process temperature**

Any

---

**Process pressure / max. overpressure  
limit**

Any

---

**Components**

Installed in source container

---

**Point Level / Solids****Measuring principle**

Radiometric Limit

---

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

Activity calculation with

Applicator

---

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

---

**Process temperature**

Any

**Point Level / Solids**

**Process pressure / max. overpressure limit**  
Any

---

**Components**  
Installed in source container

---

**Density**

**Measuring principle**  
Radiometric Density

---

**Characteristic / Application**  
Source  
Isotope: Cobalt 60  
Half-life: 5.3 years

---

**Ambient temperature**  
-20 °C ... 250 °C  
(-4 °F ... 482 °F)

---

**Process temperature**  
Any

---

**Process pressure**  
Any

---

**Specialities**  
Double seal  
Steel: 1.4541 (321 S 18)  
Classification: C66646 ISO  
2919  
Activity calculation with  
Applicator

---

Thông tin bổ sung [www.apsc.endress.com/FSG61](http://www.apsc.endress.com/FSG61)