

TR63

Explosion-proof Pt100 Thermometer

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/TR63

Lợi ích:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), flameproof (Ex d), non-sparking (Ex nA)
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- Optionally fast response time with tapered tip form
- Variable selection of process connections: thread, compression fitting or flange
- Extension neck, nipple union version, to protect the head transmitter from overheating
- Marine approval

Tổng quan về thông số kỹ thuật

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration $t_{50} = 4$ s $t_{90} = 8$ s
- **Max. process pressure (static)** at 20 °C: 100 bar (1.450 psi)
- **Operating temperature range** PT100 TF StrongSens: -50 °C ...500 °C (-58 °F ...932 °F) PT100 WW: -200 °C ...600 °C (-328 °F ...1.112 °F) PT100 TF: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

Phạm vi ứng dụng: The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust protection tubes and special materials. An optional head transmitter with all common

communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. Flexible configuration possible.

Tín năng và thông số kỹ thuật

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

US style
 modular temperature assembly
 for heavy duty applications
 suitable for hazardous areas
 flanged process connection
 with neck
 incl. thermowell / protection tube (metal)

Thermowell / protection tube

welded protection tube

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

1/4" SCH80
 1/2" SCH80
 1/2" SCH40
 3/4" SCH80
 3/4" SCH40

Max. immersion length on request

up to 10.000,00 mm (393,70")

Material protection tube/ thermowell

1.4404 (316)
 1.4749 (~446)

Thermometer**Optional coating**Not defined

Process connection

male thread:

NPT1/2"

NPT3/4"

NPT1"

flange:

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

ASME 1" 600 RF (B16.5)

ASME 1,5" 150 RF (B16.5)

ASME 1,5" 300 RF (B16.5)

ASME 1,5" 600 RF (B16.5)

ASME 2" 300 RF (B16.5)

ASME 2" 600 RF (B16.5)

Tip shape

straight

reduced

Surface roughness RaNot defined

Operating temperature range

PT100 TF StrongSens:

-50 °C ...500 °C

(-58 °F ...932 °F)

PT100 WW:

-200 °C ...600 °C

(-328 °F ...1.112 °F)

PT100 TF:

-50 °C ...400 °C

(-58 °F ...752 °F)

Max. process pressure (static)at 20 °C: 100 bar (1.450 psi)

Thermometer**Accuracy**

class A acc. to IEC 60751
class AA acc. to IEC 60751

Response time

depending on configuration
t50 = 4 s
t90 = 8 s

Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Ex - approvals

ATEX II
IECEX
EAC Ex
Explosion proof

Certification

Gost Metrology
SIL (transmitter only)
Marine approval

Thông tin bổ sung www.apsc.endress.com/TR63