

# Cell growth and biomass sensor OUSBT66

## Hygienic NIR absorption measurement in fermentation and crystallization applications



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/OUSBT66](http://www.apsc.endress.com/OUSBT66)

### Lợi ích:

- Real-time measurement for optimized processes and product yields
- Reliable, precise measured values with excellent laboratory correlation
- Easy verification and calibration with NIST-traceable clip-on filters - no need for complex liquid calibrations
- Hygienic stainless steel body and sapphire windows without seals or crevices
- Suitable for CIP/SIP and autoclaving
- Various path lengths and sensor lengths for perfect fit into every fermenter and bioreactor
- PG 13.5 thread for standard assemblies or head plate installations

### Tổng quan về thông số kỹ thuật

- **Measurement range** 0 to 4 AU 0 to 8 OD (depending on optical path length)
- **Process temperature** 0 to 90 °C (32 to 194 °F) Max. 135 °C for max. 2 hours
- **Process pressure** Max. 10 bar abs at 90 °C (Max. 150 psi at 194 °F)

**Phạm vi ứng dụng:** The OUSBT66 NIR absorption sensor monitors cell growth, biomass processes, algae systems and crystallization processes. It provides you with reliable, precise measured values in real-time to optimize your process and your product yield. The sensor's hygienic design is CIP/SIP resistant and allows autoclaving. Equipped with NIST-traceable and certified clip-on filters, OUSBT66 is outstandingly easy to calibrate and verify.

### Tín năng và thông số kỹ thuật

## Concentration

### Measuring principle

Cell growth

---

### Application

Cell growth and biomass in fermentation processes  
Monitoring of algae concentration  
Control of crystallization processes  
Suspended solids measurement

---

### Measurement range

0 to 4 AU  
0 to 8 OD (depending on optical path length)

---

### Design

Hygienic design:  
Sterilizable and autoclaveable  
Sapphire windows without seals and crevices  
CIP/SIP resistant

---

### Material

Sensor housing: Stainless Steel 1.4435 (316L)  
Windows: Sapphire  
O-ring: EPDM

---

### Process temperature

0 to 90 °C (32 to 194 °F)  
Max. 135 °C for max. 2 hours

---

### Process pressure

Max. 10 bar abs at 90 °C  
(Max. 150 psi at 194 °F)

---

### Ingres protection

IP68

---

Thông tin bổ sung [www.apsc.endress.com/OUSBT66](http://www.apsc.endress.com/OUSBT66)