

TAF12S

High temperature TC thermometer

Applicable for ceramic baking ovens, brickworks, porcelain production and glass industries



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/TAF12S

Lợi ích:

- Long lifetime by usage of innovative thermowell materials with increased wear and chemical resistance
- Long term stable measurement due to sensor protection with non-porous materials
- Flexible product selection by modular design
- Optimized life cycle costs by means of replaceable spare parts

Tổng quan về thông số kỹ thuật

- **Accuracy** class 2 acc. to IEC 60584
- **Max. process pressure (static)** at 20 °C: 1 bar (15 psi)
- **Operating temperature range** Type S: 0 C ...1.600 C (32 F ...2.912 F) Type R: 0 C ...1.600 C (32 F ...2.912 F) Type B: 600 C ...1.700 C (1.112 F ...3.092 F)
- **Max. immersion length on request** up to 2.500,00 mm (98,43")

Phạm vi ứng dụng: Measuring points with extremely high process temperatures require these special thermometers with ceramic thermowells and thermocouples made from special metals, such as platinum and rhodium. The thermowell made from ceramic materials serves as protection from mechanical and chemical damages in the process and increases the life span of the used sensors. This leads to: Cost savings for maintenance of the measuring point, quality improvements of the products and increased plant safety.

Tín năng và thông số kỹ thuật

Thermometer

Measuring principle

Thermocouple

Characteristic / Application

metric style

modular temperature assembly

high temperature (furnace)

incl. single ceramic thermowell

Thermowell / protection tube

ceramic protection tube

Insert / probe

ceramic capillary, rigid

Outer diameter protection tube / Insert

9,0 mm (0,35")

Max. immersion length on request

up to 2.500,00 mm (98,43")

Material protection tube/ thermowell

Ceramic (C610/C799)

Process connection

compression fitting:

G1/2"

G3/4"

G1"

adjustable Flange

Thermometer

Tip shape

straight

Operating temperature range

Type S:

0 C ...1.600 C

(32 F ...2.912 F)

Type R:

0 C ...1.600 C

(32 F ...2.912 F)

Type B:

600 C ...1.700 C

(1.112 F ...3.092 F)

Max. process pressure (static)

at 20 °C: 1 bar (15 psi)

Accuracy

class 2 acc. to IEC 60584

Integration head transmitteryes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)**Certification**

SIL (transmitter only)

Thông tin bổ sung www.apsc.endress.com/TAF12S