

# Ultrasonic measurement Time-of-Flight Prosonic FDU95

Ultrasonic sensor for level measurement for connection to FMU9x (measuring range up to 45m)



## Lợi ích:

- Integrated temperature sensor for Time-of-Flight correction. Accurate measurements are possible, even if temperature changes are present
- Suited for rough ambient conditions thanks to separate installation from the transmitter (up to 300m)
- Reduced build-up formation because of the self-cleaning effect
- Integrated automatic sensor detection for transmitters FMU90/ FMU95 for simple commissioning
- Weather resistant and flood-proof (IP 68)
- Non-contact measurement method minimizes service requirements
- International Dust-Ex and Gas-Ex certificates available

Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/FDU95](http://www.apsc.endress.com/FDU95)

## Tổng quan về thông số kỹ thuật

- **Process temperature** -40 °C...80 °C or 150 °C, (-40 °F...176 °F or 302 °F)
- **Process pressure / max. overpressure limit** 0.7 bar...1.5 bar abs (10 psi...22 psi)
- **Max. measurement distance** 45 m (148 ft)
- **Accuracy** +/- 2 mm + 0.17% of measured distance
- **Main wetted parts** UP (unsaturated polyester) Silicon / Al PTFE coated

**Phạm vi ứng dụng:** The FDU95 ultrasonic sensor for continuous, non-contact and maintenance-free level measurement of powdery to coarse bulk materials. The measurement is unaffected by dielectric constant, density or humidity and also unaffected by build-up due to the self-

cleaning effect of sensors. Suited for explosion hazardous areas.  
Maximum measuring range in solids 45m (148ft).

## Tín năng và thông số kỹ thuật

### Continuous / Liquids

**Measuring principle**

Ultrasonic

**Characteristic / Application**

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300 m in-between sensor and transmitter

**Supply / Communication**

4-wire (HART, Profibus DP)

**Accuracy**

+/- 2 mm + 0.17% of measured distance

**Ambient temperature**

-40 °C...80 °C  
or 150 °C,  
(-40 °F...176 °F  
or 302 °F)

**Process temperature**

-40 °C...80 °C  
or 150 °C,  
(-40 °F...176 °F  
or 302 °F)

**Process pressure / max. overpressure limit**

0.7 bar...1.5 bar abs  
(10 psi...22 psi)

**Main wetted parts**

UP (unsaturated polyester)  
Silicon / Al PTFE coated

---

**Continuous / Liquids****Process connection**

G / NPT 1"

---

**Blocking distance**0.7 m / 80 °C,  
(2.3 ft / 176 °F),  
0.9 m / 150 °C,  
(2.9 ft / 302 °F)

---

**Max. measurement distance**

45 m (148 ft)

---

**Communication**Transmitter:  
4...20 mA HART  
Profibus DP

---

**Certificates / Approvals**

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

---

**Options**

Second 4...20 mA output

---

**Components**Transmitter:  
FMU90, FMU95

---

**Continuous / Solids****Measuring principle**

Ultrasonic

---

**Characteristic / Application**

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300m in-between sensor and transmitter

---

**Supply / Communication**

4-wire (HART , Profibus DP)

---

**Continuous / Solids****Accuracy**

+/- 2mm + 0.17% of measured distance

---

**Ambient temperature**

-40 °C ... 80 °C  
or 150 °C  
(-40 °F ... 176 °F  
or 302 °F)

---

**Process temperature**

-40 °C ... 80 °C  
or 150 °C  
(-40 °F ... 176 °F  
or 302 °F)

---

**Process pressure / max. overpressure limit**

0.7 bar...1.5 bar abs  
(10 psi...22 psi)

---

**Main wetted parts**

UP (unsaturated polyester)  
Silicon / PE foam (80°C / 176°F)  
Silicon / stainless steal (150°C / 302°F)

---

**Process connection**

G / NPT 1"

---

**Blocking distance**

0.7 m / 80 °C  
(2.3 ft / 176 °F)  
0.9 m / 150 °C  
(2.9 ft / 302 °F)

---

**Max. measurement distance**

45 m (148 ft)

---

## Continuous / Solids

### Communication

Transmitter:  
4 ... 20 mA HART  
Profibus DP

---

### Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

---

### Options

Second 4...20mA output

---

### Components

Transmitter:  
FMU90

---

Thông tin bổ sung [www.apsc.endress.com/FDU95](http://www.apsc.endress.com/FDU95)