

# Proline Cubemass C 500 Coriolis flowmeter

Compact sensor for smallest quantities, with a remote transmitter version with up to 4 I/Os



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/8C5B](http://www.apsc.endress.com/8C5B)

## Lợi ích:

- Space-saving installation – compact single-tube design
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Suitable for skids – lightweight sensor
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

## Tổng quan về thông số kỹ thuật

- **Max. measurement error** Mass flow (liquid):  $\pm 0.10\%$  Volume flow (liquid):  $\pm 0.10\%$  Mass flow (gas):  $\pm 0.50\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 1000 kg/h (0 to 37 lb/min)
- **Medium temperature range**  $-50$  to  $+205 \text{ }^\circ\text{C}$  ( $-58$  to  $+401 \text{ }^\circ\text{F}$ )
- **Max. process pressure** PN 40, Class 300, 10K, 400 bar (5800 psi)
- **Wetted materials** Measuring tube: 1.4539 (904L) Connection: 1.4539 (904L); 1.4404 (316/316L)

**Phạm vi ứng dụng:** Cubemass C is the ideal sensor for the measurement of smallest flow rates in skids, test rigs and industrial robotics. Neither high pressure nor alternating flow conditions compromise its accuracy. With its innovative remote transmitter Cubemass C 500 maximizes installation flexibility and operational safety in demanding environments. Heartbeat Technology ensures measurement reliability and compliant verification.

---

## Tín năng và thông số kỹ thuật

---

Gas

### Measuring principle

Coriolis

---

### Product headline

Compact sensor for smallest quantities, with a transmitter remote version with up to 4 I/Os.

Measuring accurately smallest quantities of liquids and gases.

---

### Sensor features

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ( $\frac{1}{2}$ " to  $\frac{1}{4}$ "). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

---

### Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

---

### Nominal diameter range

DN 1 to 6 ( $\frac{1}{2}$ " to  $\frac{1}{4}$ ")

---

### Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

## Gas

**Max. measurement error**Mass flow (liquid):  $\pm 0.10\%$ Volume flow (liquid):  $\pm 0.10\%$ Mass flow (gas):  $\pm 0.50\%$ Density (liquid):  $\pm 0.0005\text{ g/cm}^3$ **Measuring range**

0 to 1000 kg/h (0 to 37 lb/min)

**Max. process pressure**

PN 40, Class 300, 10K, 400 bar (5800 psi)

**Medium temperature range** $-50$  to  $+205\text{ }^\circ\text{C}$  ( $-58$  to  $+401\text{ }^\circ\text{F}$ )**Ambient temperature range**Standard:  $-40$  to  $+60\text{ }^\circ\text{C}$  ( $-40$  to  $+140\text{ }^\circ\text{F}$ )Option:  $-50$  to  $+60\text{ }^\circ\text{C}$  ( $-58$  to  $+140\text{ }^\circ\text{F}$ )**Sensor housing material**

1.4301 (304), corrosion resistant

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L)

**Transmitter housing material**

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

**Degree of protection**

Sensor remote version (standard): IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, Type 4X enclosure

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

**Gas****Outputs**

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

**Inputs**

Status input

4-20 mA input

**Digital communication**

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

**Hazardous area approvals**

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

**Product safety**

CE, C-tick, EAC marking

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Gas****Pressure approvals and certificates**CRN

---

**Material certificates**3.1 material

---

**Liquids****Measuring principle**Coriolis

---

**Product headline**

Compact sensor for smallest quantities, with a transmitter remote version with up to 4 I/Os.

Measuring accurately smallest quantities of liquids and gases.

---

**Sensor features**

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ " ). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

---

**Nominal diameter range**DN 1 to 6 ( $\frac{1}{24}$  to  $\frac{1}{4}$ " )

---

**Wetted materials**

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

---

## Liquids

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.10$  %

Volume flow (liquid):  $\pm 0.10$  %

Mass flow (gas):  $\pm 0.50$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

### Measuring range

0 to 1000 kg/h (0 to 37 lb/min)

---

### Max. process pressure

PN 40, Class 300, 10K, 400 bar (5800 psi)

---

### Medium temperature range

-50 to +205 °C (-58 to +401 °F)

---

### Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

### Sensor housing material

1.4301 (304), corrosion resistant

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L)

---

### Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

---

### Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, Type 4X enclosure

---

### Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

---

## Liquids

### Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

---

### Inputs

Status input

4-20 mA input

---

### Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

---

### Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

---

### Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

---

### Product safety

CE, C-tick, EAC marking

---

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

## Liquids

### Pressure approvals and certificates

CRN

---

### Material certificates

3.1 material

---

Thông tin bổ sung [www.apsc.endress.com/8C5B](http://www.apsc.endress.com/8C5B)