

Ultrasonic measurement Time-of-Flight Prosonic FMU40

Cost effective device for sophisticated level measurement in liquids and bulk solids for up to 5m



F L E X

Lợi ích:

- Reliable non-contact measurement
- Quick and simple commissioning via menu-guided on-site operation with four-line plain text display, 7 languages selectable
- Envelope curves on the on-site display for simple diagnosis
- Hermetically sealed and potted sensor
- Chemically resistant sensor out of PVDF
- Calibration without filling or discharging
- Integrated temperature sensor for automatic correction of the temperature dependent sound velocity

Tổng quan về thông số kỹ thuật

- **Accuracy** +/- 2 mm or +/- 0.2 % of set measuring range
- **Process temperature** -40 °C ... 80 °C (-40 °F ... 176 °F)
- **Process pressure absolute / max. overpressure limit** 0.7 bar ... 3 bar abs (10 psi ... 44 psi)
- **Max. measurement distance** Max. measurement distance
- **Main wetted parts** PVDF

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/FMU40

Phạm vi ứng dụng: The Prosonic FMU40 sensor is suited for non-contact level measurement in fluids, pastes, coarse bulk material and flow measurement in open channels or at weirs. The two-wire or four-wire compact transmitter can be used in applications with storage tanks, agitators, on stockpiles and conveyor belts. The envelope curve can be shown on the on-site display for simple diagnosis. Linearization function

(up to 32 points) for conversion of the measured value into any unit of length, volume or flow rate.

Tín năng và thông số kỹ thuật

Continuous / Liquids

Measuring principle

Ultrasonic

Characteristic / Application

Compact ultrasonic transmitter

Supply / Communication

2/4-wire (HART), PROFIBUS PA, FOUNDATION
Fieldbus

Accuracy

+/- 2 mm or +/- 0.2 % of set measuring range

Ambient temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process pressure absolute / max. overpressure limit

0.7 bar ... 3 bar abs
(10 psi ... 44 psi)

Main wetted parts

PVDF

Process connection

G / NPT 1 1/2"

Blocking distance

0.25 m (0.8 ft)

Continuous / Liquids**Application**

Application

Max. measurement distance

Max. measurement distance

Communication

4 ... 20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, TIIS, INMETRO, NEPSI

Application limits

Application limits

Point Level / Solids**Measuring principle**

Ultrasonic Limit

Characteristic / Application

Compact ultrasonic transmitter

Supply / Communication

2/4-wire (HART),

PROFIBUS PA,

FOUNDATION Fieldbus

Ambient temperature

-40 °C...+80 °C

(-40 °F...+176 °F)

Point Level / Solids**Process temperature**

-40 °C...+80 °C

(-40 °F...+176 °F)

Process pressure absolute / max. overpressure limit

0.7 bar...3 bar abs

(10 psi...44 psi)

Main wetted parts

PVDF

Process connection

G / NPT 1 1/2"

Blocking distance

0.25 m (0.8 ft)

Communication

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, INMETRO, NEPSI

Application limits

Take notice of range diagram

Liquids**Measuring principle**

Ultrasonic

Liquids

Product headline

Compact ultrasonic measuring instrument
Cost effective solution for open channel

Max. measurement error

Low accuracy

Measuring range

0,25...5m [0.8...16ft]

Max. process pressure

atm.

Medium temperature range

-40°C ... 80°C
(-40°F...176°F)

Degree of protection

IP68

Outputs

4...20mA(Hart),PA,FF

Inputs

2-wire 16-36V DC,
4-wire 16-36V DC,
90-253V AC 50/60Hz

Digital communication

PROFIBUS PA, FOUNDATION Fieldbus

Hazardous area approvals

ATEX, FM, CSA

Continuous / Solids

Measuring principle

Ultrasonic

Continuous / Solids**Characteristic / Application**

Compact ultrasonic transmitter

Supply / Communication

2/4-wire (HART), PROFIBUS PA, FOUNDATION
Fieldbus

Accuracy

+/- 2 mm or +/- 0.2 % of set measuring range 1)

Ambient temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process pressure absolute / max. overpressure limit

0.7 bar ... 3 bar abs
(10 psi ... 44 psi)

Main wetted parts

PVDF

Process connection

G / NPT 1 1/2"

Blocking distance

0.25 m (0.8 ft)

Max. measurement distance

2 m (6 ft)

Communication

4 ... 20 mA HART
PROFIBUS PA
FOUNDATION Fieldbus

Continuous / Solids**Certificates / Approvals**

ATEX, FM, CSA, TIIS, INMETRO, NEPSI

Application limits

Take notice of range diagram

Point Level / Liquids**Measuring principle**

Ultrasonic Limit

Characteristic / Application

Compact ultrasonic transmitter

Supply / Communication

2/4-wire (HART),

PROFIBUS PA,

FOUNDATION Fieldbus

Ambient temperature

-40 °C...+80 °C

(-40 °F...+176 °F)

Process temperature

-40 °C...+80 °C

(-40 °F...+176 °F)

Process pressure absolute / max. overpressure limit

0.7 bar...3 bar abs

(10 psi...44 psi)

Main wetted parts

PVDF

Point Level / Liquids

Process connection

G / NPT 1 1/2"

Blocking distance

0.25 m (0.8 ft)

Communication

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, INMETRO, NEPSI

Application limits

Take notice of range diagram

Thông tin bổ sung www.apsc.endress.com/FMU40