

# Promag 50P



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/50P](http://www.apsc.endress.com/50P)

## Lợi ích:

- Versatile applications – wide variety of wetted materials
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Fast commissioning – application-specific Quick Setups
- Safe operation – display provides easily readable process information
- Fully industry compliant – IEC/EN/NAMUR

## Tổng quan về thông số kỹ thuật

- **Max. measurement error**  $\pm 0.5\%$   $\pm 0.2\%$  (optional)
- **Measuring range** 0...9'600 m<sup>3</sup>/h
- **Medium temperature range** -40...+180°C (-40...+356°F)
- **Max. process pressure** PN10...40 CI 150...300 JIS 10...20K AS 2129 Table E AS 4087 PN16

**Phạm vi ứng dụng:** Promag P is the preferred sensor for applications with highest requirements in a multitude of industries. Combined with the proven Promag 50 transmitter with push buttons, Promag 50P offers highly accurate measurement of liquids for a wide range of applications. Promag 50P is dedicated to chemical and process applications with corrosive liquids and high medium temperatures. Promag 50P is available as compact or remote version.

## Tín năng và thông số kỹ thuật

Liquids

Measuring principle

Electromagnetic

## Liquids

### Product headline

std\_productprofile\_product\_usp\_34684\_1508942319.

Dedicated to chemical and process applications with corrosive liquids and medium temperatures.

### Sensor features

Diverse applications – wide variety of wetted materials. Energy-saving flow measurement – no pressure loss due to cross section constriction. Maintenance-free, no moving parts.

Nominal diameter: max. DN 600 (24"). All common Ex approvals. Liner material: metal or PFA.

### Transmitter features

std\_productprofile\_product\_benefits\_34681\_1508942231.

std\_productprofile\_product\_benefits\_34683\_1508942232.

std\_productprofile\_product\_benefits\_34682\_1508942239.

std\_successorproducts\_product\_differentiating\_tech\_features\_35305\_1

std\_successorproducts\_product\_differentiating\_tech\_features\_35308\_1

std\_successorproducts\_product\_differentiating\_tech\_features\_35309\_1

### Nominal diameter range

DN 15...600

1/2"...24"

### Max. measurement error

±0.5%

±0.2% (optional)

### Measuring range

0...9'600 m<sup>3</sup>/h

### Max. process pressure

PN10...40

CI 150...300

JIS 10...20K

AS 2129 Table E

AS 4087 PN16

---

## Liquids

**Medium temperature range**

-40...+180°C  
(-40...+356°F)

---

**Ambient temperature range**

-20...+60°C  
-40...+60°C (optional)

---

**Degree of protection**

IP 67 (NEMA 4x)  
IP 68 (Nema 6P)

---

**Display/Operation**

Two line display with backlit  
Push button

---

**Outputs**

4...20 mA  
Pulse/Frequency  
Status

---

**Inputs**

Status

---

**Digital communication**

HART  
PROFIBUS PA

---

**Hazardous area approvals**

ATEX, IECEX, NEPSI, FM, CSA

---

**Product safety**

CE, C-tick, EAC marking

---

**Pressure approvals and certificates**

PED, CRN

---

Thông tin bổ sung [www.apsc.endress.com/50P](http://www.apsc.endress.com/50P)