

Digital pH sensor Memosens CPS61E

Memosens 2.0 glass sensor for the food & beverage industry and for bioreactors in biotech industry



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/CPS61E

Lợi ích:

- Memosens 2.0 offers extended storage of calibration and process data, enabling better trend identification and providing a future-proof basis for predictive maintenance and enhanced IIoT services.
- The sensor's exceptional accuracy and reproducibility help you to keep the pH value in the optimum range for a maximized product yield.
- A special glass membrane and reference system makes the sensor CIP/SIP and autoclaving resistant (up to 140°C/284°F) offering maximum long-term stability.
- The sensor protects your product quality with its certified biocompatibility according to USP class VI, FDA compliance of wetted parts, VO 1935/2004 compliance, no cytotoxicity, bioreactivity or animal-based materials.
- Streamline maintenance of CPS61E with the Memobase Plus software that automatically stores and documents all relevant sensor and process data.
- Maximum process safety through non-contact, inductive signal transmission
- Reduced operating costs thanks to minimized process downtime and extended sensor lifetime.

Tổng quan về thông số kỹ thuật

- **Measurement range** pH: 0 to 14
- **Process temperature** Application N: 0 to 100 °C (32 to 212 °F) Up to 140 °C (284 °F) for sterilization
- **Process pressure** 0.8 to 7 bar (11.6 to 101.5 psi) absolute

Phạm vi ứng dụng: Keep the pH value in the optimum range and maximize your product yield with Memosens CPS61E. Its rugged design and long-term stability ensure extremely accurate and reproducible measured values even after CIP/SIP or autoclaving. CPS61E features Memosens 2.0 digital technology, offering extended storage of calibration and process data for predictive maintenance. The sensor resists moisture and enables lab calibration, enhancing process integrity and increasing process uptime.

Tín năng và thông số kỹ thuật

pH

Measuring principle

Potentiometric

Application

Hygienic and sterile applications (sterilizable, autoclavable):

- Bioreactor/fermenter
- Biotechnology
- Pharmaceutical industry
- Foods

Characteristic

Digital pH electrodes for hygienic production processes with ion trap for long-term stable reference

Measurement range

pH: 0 to 14

Measuring principle

Gel compact electrode with ceramic junction and ion trap

| | |
|--|--|
| pH | Design |
| | All shaft lengths with temperature sensor Advanced gel technology |
| | Material |
| | Sensor shaft: Glass to suit process |
| | pH membrane glass: Type N |
| | Metal lead: Ag/AgCl |
| | Open aperture: Ceramic junction, zirconium dioxide |
| | O-ring: FKM |
| | Process coupling: PPS fiber-glass reinforced |
| | Nameplate: Ceramic metal oxide |
| Dimension | |
| Diameter: 12 mm (0.47 inch) Shaft lengths: 120, 225, 360 and 425 mm (4.72, 8.86, 14.2 and 16.7 inch) | |
| Process temperature | |
| Application N: 0 to 100 °C (32 to 212 °F) Up to 140 °C (284 °F) for sterilization | |
| Process pressure | |
| 0.8 to 7 bar (11.6 to 101.5 psi) absolute | |
| Temperature sensor | |
| NTC 30k | |

pH

Ex certification

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals for use in hazardous areas Zone 0, Zone 1 and Zone 2.

Connection

Inductive, contactless connection head with Memosens 2.0 technology

Ingres protection

IP68

Thông tin bổ sung www.apsc.endress.com/CPS61E