

RID16

8 channel field indicator for fieldbuses

Indication of up to 8 process or calculated values for FOUNDATION Fieldbus™ or PROFIBUS® PA protocol



từ **478,00 €**

Giá kể từ 24.01.2022

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/RID16

Lợi ích:

- Simple and standardized communication via fieldbus protocol
- Listener mode for up to 8 analog channels or digital status
- Brilliant, back lit LC display with bargraph, diagnostic symbols and clear text field
- No external power supply required
- International approvals

Tổng quan về thông số kỹ thuật

- **Input** Foundation Fieldbus protocol PROFIBUS PA protocol
- **Output** Not defined
- **Display** High contrast backlit LCD with bargraph TAG/unit
- **Power Supply** Not defined

Phạm vi ứng dụng: The 8 channel indicator shows measured and calculated values, and status information of the fieldbus users in a FOUNDATION Fieldbus™ or PROFIBUS® PA network. In the listener mode the device listens to the set fieldbus addresses and indicates their values. In addition, for FOUNDATION Fieldbus™ values available on the bus can be indicated via function block interconnection. A plain text field allows the display of the engineering unit or of the TAG. A bargraph is available for trend visualization.

Tín năng và thông số kỹ thuật

Process indicator & control units**Measuring principle**
Fieldbus indicators

Measuring principle
8 channel field indicator for fieldbuses

Function
Display values
Advanced diagnostic

Display
High contrast backlit LCD with bargraph
TAG/unit

Power Supply
Not defined

Input
Foundation Fieldbus protocol
PROFIBUS PA protocol

Output
Not defined

Output
Not defined

Software functions
Listener Mode
On Foundation Fieldbus also function block
connection:
Display transducer block
Advanced diagnostic block
2 x input selector
Arithmetic block
Integrator block
PID block

Process indicator & control units

Certificates
ATEX Ex ia
FM
CSA
IECEX Ex ia

SIL
Not defined

Panel mounting
field

Acquisition / Evaluation

Measuring principle
Display

Function
Display values
Advanced diagnostic

Certification
ATEX Ex ia
FM
CSA
IECEX Ex ia

Input
Foundation Fieldbus protocol
PROFIBUS PA protocol

Dimensions (wxhxd)
Field housing:
199 x 133 x 96 mm
(7.83 x 5.24" x 3.78")

Acquisition / Evaluation

Software

Listener Mode

On Foundation Fieldbus also function block connection:

Display transducer block

Advanced diagnostic block

2 x input selector

Arithmetic block

Integrator block

PID block

Operation

Foundation Fieldbus: via fieldbus

PROFIBUS PA: DTM and FieldCare or DIP-switches on the device

Write lock on hardware

Display

High contrast backlit LCD with bargraph

TAG/unit

Operating Voltage

9-32 V DC, polarity independent

Thông tin bổ sung www.apsc.endress.com/RID16