

# TC61

## Explosion-proof TC thermometer with DIN thermowell

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/TC61](http://www.apsc.endress.com/TC61)

### Lợi ích:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), flameproof (Ex d), non-sparking (Ex nA)
- High degree of insert compatibility and design as per DIN 43772
- Extension neck to protect the head transmitter from overheating
- Fast response time with reduced/tapered tip form
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths

### Tổng quan về thông số kỹ thuật

- **Accuracy** class 1 acc. to IEC 60584
- **Response time** depending on configuration  $t_{50} = 3$  s  $t_{90} = 7$  s
- **Max. process pressure (static)** at 20 °C: 100 bar (1.450 psi)
- **Operating temperature range** Type K: -40 °C ...1.100 °C (-40 °F ...2.012 °F) Type J: -40 °C ...750 °C (-40 °F ...1.382 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Phạm vi ứng dụng:** The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust protection tubes and special materials. An optional head transmitter with all common communication protocols makes the device ready to use with enhanced

measurement accuracy and reliability compared to directly wired sensors.  
Flexible configuration possible.

## Tín năng và thông số kỹ thuật

### Thermometer

#### Measuring principle

Thermocouple

#### Characteristic / Application

metric style

modular temperature assembly

for heavy duty applications

suitable for hazardous areas

with neck

incl. thermowell / protection tube (metal)

#### Thermowell / protection tube

welded protection tube

#### Insert / probe

mineral insulated (MI), flexible

#### Outer diameter protection tube / Insert

9,0 mm (0,35")

11,0 mm (0,43")

12,0 mm (0,47")

#### Max. immersion length on request

up to 10.000,00 mm (393,70")

Thermometer

**Material protection tube/ thermowell**

1.4404 (316L)

1.4571 (316Ti)

Alloy 600 (2.4816)

Alloy C276 (2.4819)

---

**Optional coating**

Not defined

---

## Thermometer

**Process connection**

male thread:

G1/2"

G3/4"

G1"

NPT1/2"

NPT3/4"

M20x1,5

compression fitting:

G1/2"

G1"

flange:

DN25 PN40 B1 (EN1092)

DN40 PN40 B1(EN1092)

DN50 PN40 B1 (EN1092)

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

---

## Thermometer

**Tip shape**

straight

reduced

tapered

**Surface roughness Ra**

0,8 µm (31,5 µin.)

**Operating temperature range**

Type K:

-40 °C ...1.100 °C

(-40 °F ...2.012 °F)

Type J:

-40 °C ...750 °C

(-40 °F ...1.382 °F)

**Max. process pressure (static)**

at 20 °C: 100 bar (1.450 psi)

**Accuracy**

class 1 acc. to IEC 60584

**Response time**

depending on configuration

t50 = 3 s

t90 = 7 s

Thermometer

**Integration head transmitter**

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

---

**Ex - approvals**

ATEX II

IECEX

NEPSI

EAC Ex

Explosion proof

---

**Certification**

Gost Metrology

SIL (transmitter only)

---

Thông tin bổ sung [www.apsc.endress.com/TC61](http://www.apsc.endress.com/TC61)