

Turbimax CUE24



Lợi ích:

- Easy verification of your entire process
- Easy verification of your online measurement loops
- Guided calibration according to predefined standards

Phạm vi ứng dụng: Turbimax CUE24 is a reliable turbidity meter for grab sample measurement compliant to US EPA 180.1. It offers verification of your online turbidity measurements and lab-based control of your processes. Operation is simple: fill the cuvette, insert it into the measuring chamber and get an instant reading. In addition, Turbimax CUE24 provides guided calibration according to predefined standards, helping to streamline maintenance.

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/CUE24

Tín năng và thông số kỹ thuật

Turbidity

Measuring principle

Application

Turbidimeter for laboratory measurement

Characteristic

- " Versions with white light source
- " Auto ranging 0 ... 1000 NTU
- " Automatic alert when calibration is needed
- " Simple calibration procedures
- " RS-232 output for printing or recording of measured values
- " Reusable calibration standards

Measurement range

0 - 1000 NTU

Turbidity

Measuring principle

Turbidity measurement using standardised 90° scattered light method acc. to U.S.EPA 180.1(White Light)

Design

The transmitted infrared light beam is scattered by the solid matter particles in the medium. The scattered light beams are detected by scattered light receivers which are arranged at an angle of 90° to the light source.

Material

Housing: ABS

Sample cuvette: Borosilicate glass

Dimension

95 x 254 x 273 mm / 3.75 x 10 x 10.75 inches

Process temperature

0 ... 50 °C / 32 ... 122 °F

Process pressure

Ambient pressure

Output / communication

Uni-directional RS-232 output for recorder

Thông tin bổ sung www.apsc.endress.com/CUE24