

RNB130

Primary switched-mode power supply for DIN rail

Power supply for one 4 wire sensor or transmitter.



Lợi ích:

- Small housing, 35 mm width
- High availability
- Wide range input - can be used world-wide
- Power reserve (Power Boost)
- Power supply without wiring: Supply via DIN rail bus connector
- Space saving DIN rail mounting as per IEC 60715

Tổng quan về thông số kỹ thuật

- **Output** 24 VDC, 1,5 A
- **Power Supply** 100...240 V AC (wide range power supply) 45...65 Hz

từ **142,00 €**

Giá kể từ 16.09.2021

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/RNB130

Phạm vi ứng dụng: The power supply has one output for supplying voltage to 4 wire sensors and transmitters. Connection to mono-phased a.c. networks or to two phase conductors of three-phase supply networks (TN-, TT- or IT-networks as per VDE 0100 T 300/IEC 364-3) with 100-240 V AC nominal voltage possible.

Tín năng và thông số kỹ thuật

Acquisition / Evaluation

Measuring principle

Power supply

Function

Power

Acquisition / Evaluation**Output**24 VDC, 1,5 A

Auxiliary power supply / Loop power supply

85...250 V AC

45...65 Hz

Dimensions (wxhxd)

35 x 99 x 102.5 mm

(1.39" x 3.9" x 4.04")

OperationDIP switch

Power supplies & barrier**Measuring principle**Power supply

Measuring principlePower supply

FunctionPower supply for one 4-wire sensor or transmitter

Loop power supply24 V DC

Power Supply

100...240 V AC (wide range power supply)

45...65 Hz

Power supplies & barrier

Auxiliary power supply / Loop power supply

85...250 V AC

45...65 Hz

Output

24 VDC, 1,5 A

Operation

DIP switch

Thông tin bổ sung www.apsc.endress.com/RNB130