

Ultrasonic measurement Time-of-Flight Prosonic FDU93

Ultrasonic sensor for level and flow measurement for connection to FMU9x (measuring range up to 25m)



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/FDU93

Lợi ích:

- Integrated temperature sensor for Time-of-Flight correction. Accurate measurements are possible, even if temperature changes are present
- Suited for rough ambient conditions thanks to separate installation from the transmitter (up to 300m)
- Reduced build-up formation because of the self-cleaning effect
- Integrated automatic sensor detection for transmitters FMU90/ FMU95 for simple commissioning
- Weather resistant and flood-proof (IP 68)
- Non-contact measurement method minimizes service requirements
- International Dust-Ex and Gas-Ex certificates available

Tổng quan về thông số kỹ thuật

- **Process temperature** -40 °C ... 95 °C (-40 °F ... 203 °F)
- **Process pressure absolute / max. overpressure limit** 0.7 bar ... 3 bar abs (10 psi ... 43 psi)
- **Max. measurement distance** Max. measurement distance
- **Accuracy** +/- 2 mm + 0.17% of measured distance
- **Main wetted parts** UP (unsaturated polyester) Silicon / Al PTFE coated

Phạm vi ứng dụng: The FDU93 ultrasonic sensor for continuous, non-contact and maintenance-free level measurement of fluids, pastes, sludges and powdery to coarse bulk materials. But also for flow measurement in open channels and measuring weirs. The measurement is unaffected by dielectric constant, density or humidity and also

unaffected by build-up due to the self-cleaning effect of sensors. Suited for explosion hazardous areas. Maximum measuring range in liquids 25m (85ft), solids 15m (50ft).

Tín năng và thông số kỹ thuật

Continuous / Liquids

Measuring principle

Ultrasonic

Characteristic / Application

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300 mm in-between sensor and transmitter

Supply / Communication

4-wire (HART, Profibus DP)

Accuracy

+/- 2 mm + 0.17% of measured distance

Ambient temperature

-40 °C ... 95 °C
(-40 °F ... 203 °F)

Process temperature

-40 °C ... 95 °C
(-40 °F ... 203 °F)

Process pressure absolute / max. overpressure limit

0.7 bar ... 3 bar abs
(10 psi ... 43 psi)

Main wetted parts

UP (unsaturated polyester)
Silicon / Al PTFE coated

Process connection

G / NPT 1"

Continuous / Liquids**Blocking distance**0.6 m (2 ft)

ApplicationApplication

Max. measurement distanceMax. measurement distance

Communication

Transmitter:

4...20 mA HART

Profibus DP

Certificates / ApprovalsATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

OptionsSecond 4...20 mA output

Components

Transmitter:

FMU90, FMU95

Continuous / Solids**Measuring principle**Ultrasonic

Characteristic / ApplicationSeparated version with field housing or top hat rail housing for control cabinet instrumentation, 300m in-between sensor and transmitter

Supply / Communication4-wire (HART , Profibus DP)

Accuracy+/- 2mm + 0.17% of measured distance

Continuous / Solids

Ambient temperature

-40 °C ... 95 °C
(-40 °F ... 203 °F)

Process temperature

-40 °C ... 95 °C
(-40 °F ... 203 °F)

Process pressure absolute / max. overpressure limit

0.7 bar ... 3 bar abs
(10 psi ... 43 psi)

Main wetted parts

UP (unsaturated polyester)
Silicon / Al PTFE coated

Process connection

G / NPT 1"

Blocking distance

0.6 m (2 ft)

Max. measurement distance

15 m (50 ft)

Communication

Transmitter:
4 ... 20 mA HART
Profibus DP

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

Options

Second 4...20mA output

Components

Transmitter:
FMU90

Thông tin bổ sung www.apsc.endress.com/FDU93