

Liquiphant FTL62 - the coated sensor for aggressive media

A level switch for aggressive and pumpable liquids



Más información y precios actuales:

www.ar.endress.com/FTL62

Ventajas:

- Universal measuring principle for limit detection – proven vibronic technology
- Developed according IEC 61508 for highest safety – SIL2/3 applications (3rd party approved)
- Periodic proof testing is quickly and simple organized with guided wizards via the SmartBlue-App or via a test button or magnetic pin from outside. Via these ways, you can initiate the instrument for a fast and easy testing of the safety loop
- Heartbeat Technology allows safe, continuous diagnostics and a simple verification
- **Heartbeat Diagnostics:** Permanent diagnostics increase the safety of the plant. You connect your device via the SmartBlue-App and you easily have real time diagnostics at hand
- **Heartbeat Verification:** The device can be verified without process interruption. The verification report is generated automatically
- **Heartbeat Monitoring:** With the frequency tracking of the sensor data you have all information at hand for predictive maintenance and process optimization strategies

Resumen de especificaciones

- **Temperatura del proceso** -50 °C...+150 °C (-58 °F...+302 °F)
- **Presión de proceso absoluta / límite de sobrepresión máx.**
Vacuum...40 bar Vacuum...580 psi
- **Densidad min. del medio** 0.5 g/cm³ (0.4 g/cm³ optional)

Ámbito de aplicación: Liquiphant FTL62 has a strong focus on specific applications with aggressive liquids and simplicity with easy proof testing, reliability and safety (SIL) with compliance to IEC 61508, API 2350 and

WHG. The vibronic device is determined for a safe and active measuring technology in aggressive liquids and want a reliable and proven point level detection for tank overfill prevention and pump dry run protection. The FTL62 is easy to use, has a digital connection and gives a real-time data at hand.

Características y especificaciones

Nivel del Punto / Líquidos

Measuring principle

Líquidos con vibración

Característica / Aplicación

Compact vibronic device with highly corrosion-resistant coating for aggressive media,
Optional extension tube up to 3 m (9.8ft),

Modular housing concept

Especialidades

Heartbeat Technology,

Bluetooth® Operation and maintenance SmartBlue App,

LED Module,

RFID TAG for easy identification,

Second line of defense

Temperature spacer for high process temperature,

Plug and play functionalities

Nivel del Punto / Líquidos**Suministro / Comunicación**

19...253V AC / 2-wire,

10...55V / DC-PNP 3-wire,

9...20V DC with relay DPDT,

19...253V AC or 19...55V DC with relay DPDT,

2-wire NAMUR,

2-wire PFM

Temperatura ambiente

-60 °C...+70 °C

(-51 °F...+158 °F)

Temperatura del proceso

-50 °C...+150 °C

(-58 °F...+302 °F)

Presión de proceso absoluta / límite de sobrepresión máx.

Vacuum...40 bar

Vacuum...580 psi

Densidad min. del medio0.5 g/cm³(0.4 g/cm³ optional)

Nivel del Punto / Líquidos**Principales partes húmedas**

ECTFE,

PFA (Edlon, RubyRed or conductive)

316L

Enamel

Conexión a proceso

Flanges:

DN25...DN100

ASME 1"...4"

JIS 50A

Longitud del sensor

Up to 3 m (9.8ft)

Comunicación

2-wire direct load

DC-PNP 3-wire

Relays

NAMUR

PFM

Bluetooth® wireless technology

Certificados / Aprobaciones

ATEX, IEC Ex

Nivel del Punto / Líquidos

Aprobaciones de seguridad

Overfill protection WHG

SIL2/ SIL 3 according to IEC 61508

Aprobaciones de diseño

EN 10204-3.1

ASME B31.3 Process Piping

CRN

Opciones

Ambient temperature down to -60 °C (-76 °F),

Heavy duty stainless steel housing

Componentes

FTL325P Interface PFM

FTL325N Interface NAMUR

Más información www.ar.endress.com/FTL62