

TST187

Modular RTD thermometer

Comprehensive and common temperature measurement technology for almost all branches of industry



More information and current pricing:

www.at.endress.com/TST187

Benefits:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Extension neck to protect the head transmitter from overheating
- Fast response time

Specs at a glance

- **Accuracy** class A acc. to IEC 60751
- **Response time** $t_{50} = 18\text{ s}$ $t_{90} = 55\text{ s}$
- **Max. process pressure (static)** at 20 °C: 50 bar (725 psi)
- **Operating temperature range** PT 100: -50 °C ...400 °C (-58 °F ... 752 °F)
- **Max. immersion length on request** up to 400,00 mm (15,75")

Field of application: The thermometer is mainly used in the chemical industry but also finds its use in other branches. The device is equipped with a directly wired Pt100-sensor with 4-wire installation. A variety of process connections, immersion lengths and materials offer flexible application possibilities.

Features and specifications

Thermometer

Measuring principle

Resistance Temperature Detector

Thermometer**Characteristic / Application**

metric style

modular temperature assembly

threaded process connection

with neck

incl. thermowell / protection tube
(metal)

Thermowell / protection tube

welded protection tube

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

9,0 mm (0,35")

Max. immersion length on request

up to 400,00 mm (15,75")

Material protection tube/ thermowell

1.4404 (316L)

Process connection

male thread:

G1/2"

NPT1/2"

Tip shape

straight

Surface roughness Ra

0,8 µm (31,5 µin.)

Thermometer

Operating temperature range

PT 100:

-50 °C ...400 °C

(-58 °F ... 752 °F)

Max. process pressure (static)at 20 °C: 50 bar (725 psi)

Accuracyclass A acc. to IEC 60751

Response timet₅₀ = 18 st₉₀ = 55 s

Integration head transmitterno

More information www.at.endress.com/TST187