

# iTEMP TMT162

## Temperature field transmitter

Electronic monitoring, conversion and display of input signals - all over the industries



More information and current pricing:

[www.at.endress.com/TMT162](http://www.at.endress.com/TMT162)

### Benefits:

- High reliability in harsh industrial environments due to dual compartment housing and compact, fully potted electronics
- Backlit display with large measured value, bar graph and status condition indication
- Diagnostics information according to NAMUR NE107
- International approvals such as FM, CSA (IS, NI, XP and DIP) and ATEX (Ex ia, Ex nA nL, Ex d and dust ignition-proof); marine approval
- SIL certification as per IEC 61508:2010
- Galvanic isolation 2 kV (sensor input / current output)

### Specs at a glance

- **Accuracy** (Pt100, -50...200 °C)  $\leq 0,15$  K (HART) (Pt100, -58...392 °F)  $\leq 0,3$  °F (HART) (Pt100)  $\leq 0,1$  K (FF, PA) (Pt100)  $\leq 0,18$  °F (FF, PA)

**Field of application:** Unsurpassed reliability, accuracy and long-term stability in critical processes. The remote configurable transmitter transfers and monitors converted signals from RTD sensors and thermocouples as well as from resistance and voltage signals using selectively HART®, FOUNDATION Fieldbus™-, PROFIBUS® PA-communication. It visualizes the signals on its own backlit display. A field housing allows a direct connection in harsh process areas as well as in hygienic applications as option.

### Features and specifications

---

**Temperature transmitters****Measuring principle**Field transmitter

---

**Input**2 x RTD, TC, Ohm, mV

---

**Output**

FOUNDATION Fieldbus H1

PROFIBUS PA

---

**Auxiliary power supply**

11,5...42 V DC

Ex ia: 11,5...30 V DC

FOUNDATION Fieldbus:

9...32 V DC

Ex ia: 10,5...24 V DC

PROFIBUS PA:

9...32 V DC

Ex ia: 10,5...24 V DC

---

**Communication**

FOUNDATION Fieldbus

PROFIBUS PA

---

**Installation**in field

---

**Temperature transmitters****Accuracy**

(Pt100, -50...200 °C)  $\leq 0,15$  K (HART)

(Pt100, -58...392 °F)  $\leq 0,3$  °F (HART)

(Pt100)  $\leq 0,1$  K (FF, PA)

(Pt100)  $\leq 0,18$  °F (FF, PA)

---

**Galvanic isolation**

yes

---

**Temperature transmitters****Certification**

UL rec. Comp

FM IS, NI I/1+2/ABCD

CSA IS, NI I/1+2/ABCD

ATEX II1G Ex ia IIC T6

ATEX II2G Ex d IIC T6

ATEX II3G Ex nA IIC T6

ATEX II3G Ex ic IIC T6

ATEX IECEx II2D Ex tb IIIC Db

ATEX II1G Ex ia IIC T6, II2D Ex ia IIIC

FM XP, NI, DIP I,II,III/1+2/A-G

CSA XP, NI, DIP I,II,III/1+2/A-G

FM XP, DIP, IS, NI I,II,III/1+2/A-G

CSA XP, DIP, IS, NI I,II,III/1+2/A-G

FM+CSA XP,DIP, IS, NI I,II,III/1+2/A-G

CSA General Purpose

IECEX Ex d IIC T6 Gb

IECEX Ex ia, Ex d

NEPSI Ex ia IIC T4-T6

NEPSI Ex nA II T4-T6

NEPSI Ex d IIC T4-T6

## Temperature transmitters

---

More information [www.at.endress.com/TMT162](http://www.at.endress.com/TMT162)