

# Vibronic

## Point level detection

### Liquiphant FTL51

Point level switch with extension tube for liquids in all industries



More information and current pricing:

[www.at.endress.com/FTL51](http://www.at.endress.com/FTL51)

#### Benefits:

- Use in safety systems requiring functional safety to SIL2/SIL3 in accordance with IEC 61508/IEC 61511-1
- International explosion protection certificates and overfill prevention certificate (WHG)
- No calibration required, easy to start up
- No mechanically moving parts: no maintenance, no wear, long operating life.  
Monitoring of fork for damage: guaranteed function
- Second line of defense to protect the environmental
- Variety of standardized process connections for all applications
- Stainless steel (316L) and high-corrosion resistant sensor material (Alloy)

#### Specs at a glance

- **Process temperature** -50 °C...+150 °C (-58 °F...+302 °F)
- **Process pressure absolute / max. overpressure limit**  
Vacuum...100 bar
- **Min. density of medium** 0.5g/cm<sup>3</sup>(0.4g/cm<sup>3</sup> optional)

**Field of application:** Liquiphant FTL51 is a point level switch with extension tube for use in hazardous areas with all international certificates. Useable in all industries. FTL51 offers functional safety SIL2/SIL3. With the second line of defense highest degree of safety and availability of the device can be guaranteed. Reliable measurement

values, not affected by: changing media properties, flow, turbulences, gas bubbles, foam, vibrations or build-up.

## Features and specifications

### Density

#### Measuring principle

Vibration Density

#### Characteristic / Application

Liquiphant M Density  
with Density Computer FML621  
Temperature and pressure measurement  
Modular housing concept  
Wide range of process connections  
Pipe extension up to 3 m (6 m option)

#### Supply / Communication

Transmitter power supply (MUS)

#### Ambient temperature

-50...70°C  
-50...60°C for hazardous applications

#### Process temperature

0...80°C (validity of accuracy data)  
-50...0°C / 80...150 °C (with reduced technical data)

#### Process pressure absolute

0...25 bar  
>25..100 bar (with reduced technical data)

#### Wetted parts

316L/C4

#### Sensor length

115...3000 mm  
>3000...6000 mm (Option)

---

**Density****Output**

Pulse

---

**Certificates / Approvals**

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

---

**Specialities**

Commissioning with ReadWin2000

---

**Components**

Density Computer FML621

---

**Other approvals and certificates**

SIL2/ SIL3

---

**Point Level / Liquids****Measuring principle**

Vibration Liquids

---

**Characteristic / Application**

Modular housing concept

wide range of process connections

Analogue and bus interfaces

Extensive certificate range (e.g. Ex, WHG)

pipe extension up to 3m (6m option)

---

**Specialities**

Foam detection

Detect a density change

second line of defense

---

**Point Level / Liquids****Supply / Communication**

PROFIBUS PA  
19...253V AC  
10...55V DC-PNP  
19...253V AC or 10...55V DC  
8/16mA, 11...36V DC  
NAMUR  
PFM

---

**Ambient temperature**

-50 °C...+70 °C  
(-58 °F...+158 °F)

---

**Process temperature**

-50 °C...+150 °C  
(-58 °F...+302 °F)

---

**Process pressure absolute / max. overpressure limit**

Vacuum...100 bar

---

**Min. density of medium**

0.5g/cm<sup>3</sup>(0.4g/cm<sup>3</sup> optional)

---

**Main wetted parts**

316L / Alloy

---

**Process connection**

Thread:  
G3/4A, G1A, R3/4", R1, NPT3/4, NPT1  
Flange:  
DN25...DN100,  
ASME 1"...4",  
JIS 25A...100A

---

**Process connection hygienic**

Tri-Clamp ISO2852

---

---

**Point Level / Liquids****Sensor length**

Length 130mm (5.12") (Liquiphant II)  
148mm...6000mm (5.83"...236")

---

**Communication**

PROFIBUS PA  
19...253V AC  
10...55V DC-PNP  
19...253V AC bzw 10...55V DC  
8/16mA, 11...36V DC  
NAMUR  
PFM

---

**Certificates / Approvals**

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

---

**Safety approvals**

SIL2/ SIL3

---

**Design approvals**

EN 10204-3.1  
NACE MR0175, MR0103  
ASME B31.3  
AD2000

---

**Marine approval**

GL/ ABS/ DNV

---

**Options**

Heavy duty stainless steel housing mainly for the oil and gas industry

---

**Components**

FTL325P/FTL375P Interface PFM  
FTL325N/FTL375N Interface NAMUR

---

**Successor**

Liquiphant FTL51B

---

More information [www.at.endress.com/FTL51](http://www.at.endress.com/FTL51)