

Proline Promass F 100 Coriolis flowmeter

The flowmeter with premium accuracy,
robustness and an ultra-compact transmitter



More information and current pricing:

www.au.endress.com/8F1B

Benefits:

- Highest process safety – immune to fluctuating and harsh environments
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Space-saving transmitter – full functionality on smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification – Heartbeat Technology

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.1\%$ (standard), 0.05% (option) Volume flow (liquid): $\pm 0.1\%$ Mass flow (gas): $\pm 0.25\%$ Density (liquid): $\pm 0.0005\text{ g/cm}^3$
- **Measuring range** 0 to 2 200 000 kg/h (0 to 80 840 lb/min)
- **Medium temperature range** Standard: -50 to $+150\text{ }^\circ\text{C}$ (-58 to $+302\text{ }^\circ\text{F}$) Option: -50 to $+240\text{ }^\circ\text{C}$ ($-58\text{...}+464\text{ }^\circ\text{F}$)
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022) Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Field of application: Promass F has a long standing reputation as a highly accurate device under varying process conditions. It is suited for broadest range of applications. Combined with the smallest transmitter housing available today it delivers full performance on the smallest footprint. Promass F 100 will be the preferred choice for system integrators, skid builders and equipment manufacturers. Available with

an extra-compact stainless steel hygienic housing it can be placed even into the most compact rigs.

Features and specifications

Steam

Measuring principle

Coriolis

Product headline

The flowmeter with premium accuracy, robustness and an ultracompact transmitter. Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature up to $+240$ °C ($+464$ °F).

Transmitter features

Space - saving transmitter – full functionality on smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra - compact transmitter housing. High ingress protection: IP69.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Steam**Max. measurement error**Mass flow (liquid): ± 0.1 % (standard), 0.05 % (option)Volume flow (liquid): ± 0.1 %Mass flow (gas): ± 0.25 %Density (liquid): ± 0.0005 g/cm³

Measuring range0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressurePN 100, Class 600, 63K

Medium temperature rangeStandard: -50 to $+150$ °C (-58 to $+302$ °F)Option: -50 to $+240$ °C (-58 ... $+464$ °F)

Ambient temperature rangeStandard: -40 to $+60$ °C (-40 to $+140$ °F)Option: -50 to $+60$ °C (-58 to $+140$ °F)

Sensor housing material1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Display/Operation

No local operation

Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

Steam**Inputs**

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS (American Bureau of Shipping)

BV (Bureau Veritas)

LR (Lloyds Register)

BV approval

Pressure approvals and certificatesPED, CRN, AD 2000

Steam**Material certificates**

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Liquids**Measuring principle**

Coriolis

Product headline

The flowmeter with premium accuracy, robustness and an ultracompact transmitter. Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Medium temperature up to $+240\text{ }^{\circ}\text{C}$ ($+464\text{ }^{\circ}\text{F}$).

Transmitter features

Space - saving transmitter – full functionality on smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra - compact transmitter housing. High ingress protection: IP69.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Liquids

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.1 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 to $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Liquids

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Display/Operation

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Liquids

Marine approvals and certificates

ABS (American Bureau of Shipping)

BV (Bureau Veritas)

LR (Lloyds Register)

BV approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Gas

Measuring principle

Coriolis

Product headline

The flowmeter with premium accuracy, robustness and an ultracompact transmitter. Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature up to $+240$ °C ($+464$ °F).

Gas

Transmitter features

Space - saving transmitter – full functionality on smallest footprint.
Time - saving local operation without additional software and hardware
– integrated web server. Integrated verification – Heartbeat Technology.
Robust, ultra - compact transmitter housing. High ingress protection:
IP69.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602
(UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow,
reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.1 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 to $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Gas

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Display/Operation

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-Tick, EAC marking

Gas

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS (American Bureau of Shipping)

BV (Bureau Veritas)

LR (Lloyds Register)

BV approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Density/Concentration

Measuring principle

Coriolis

Product headline

The flowmeter with premium accuracy, robustness and an ultracompact transmitter. Highest measurement performance for liquids and gases under varying, demanding process conditions.

Density/Concentration

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Medium temperature up to $+240\text{ }^{\circ}\text{C}$ ($+464\text{ }^{\circ}\text{F}$).

Transmitter features

Space - saving transmitter – full functionality on smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra - compact transmitter housing. High ingress protection: IP69.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Max. measurement error

Mass flow (liquid): $\pm 0.1\%$ (standard), 0.05% (option)

Volume flow (liquid): $\pm 0.1\%$

Mass flow (gas): $\pm 0.25\%$

Density (liquid): $\pm 0.0005\text{ g/cm}^3$

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Density/Concentration**Medium temperature range**

Standard: -50 to +150 °C (-58 to +302 °F)

Option: -50 to +240 °C (-58...+464 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Display/Operation

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Density/Concentration

Product safety

CE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS (American Bureau of Shipping)

BV (Bureau Veritas)

LR (Lloyds Register)

BV approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

More information www.au.endress.com/8F1B