

# Hydrostatic Level measurement Deltapilot FMB53

## Pressure sensor with Contite measuring cell for hydrostatic level measurement



More information and current pricing:

[www.au.endress.com/FMB53](http://www.au.endress.com/FMB53)

### Benefits:

- Hermetically sealed Contite measuring cell with condensate-resistance, high reference accuracy:  $\pm 0.2\%$ , optionally  $\pm 0.1\%$  and minimum temperature effects
- Modular concept for easy replacement of display or electronics
- Seamless and independent system integration (HART/PA/FF)
- Easy and safe menu-guided operation: On-site via display module, via 4 to 20mA with HART, via PROFIBUS PA, via FOUNDATION Fieldbus
- International usage thanks to a wide range of approvals

### Specs at a glance

- **Accuracy** Standard 0.2% Optional 0.1%
- **Process temperature** PE cable:  $-10^{\circ}\text{C} \dots 70^{\circ}\text{C}$  /  $14^{\circ}\text{F} \dots 158^{\circ}\text{F}$  FEP cable:  $-10^{\circ}\text{C} \dots 80^{\circ}\text{C}$  /  $14^{\circ}\text{F} \dots 176^{\circ}\text{F}$
- **Pressure measuring range** 100mbar...10bar (1.5psi...150psi)
- **Process pressure absolute / max. overpressure limit** 40 bar (600 psi)
- **Main wetted parts** Alloy C 316L Cable (PE/FEP) optional coating AuPt optional coating AuRh

**Field of application:** The Deltapilot FMB53 is a cable version with mounting clamp. This device with the Contite measuring cell is typically used in the environmental industries. It is made for level measurement in liquid and paste-like media in open or closed containers and unaffected by possible foam formation. For use in SIL2 safety systems.

### Features and specifications

---

## Pressure

### Measuring principle

Hydrostatic pressure

---

### Characteristic

Pressure transmitter for hydrostatic level measurement with flush mounted metallic Contite measuring cell:

Hermetically sealed, condensate-resistant, climatic-proofed and with lowest temperature influences

Cable version with suspension clamp

---

### Supply voltage

4...20 mA HART

10,5...45 VDC (Non Ex):

Ex ia: 10,5...30 VDC

PROFIBUS PA:

9...32 VDC (Non Ex)

FOUNDATION Fieldbus:

9...32 VDC (Non Ex)

---

### Reference Accuracy

Standard 0.2%

Optional 0.1%

---

### Long term stability

0.05 % of URL/year

---

### Process temperature

PE cable: -10°C...70°C / 14°F...158°F

FEP cable: -10°C...80°C / 14°F...176°F

---

## Pressure

**Ambient temperature**

-40°C...85°C  
(-40°F...185°F)

---

**Measuring cell**

100 mbar...10 bar  
(1.5 psi...150 psi)

---

**Smallest calibratable span**

10 mbar (1.45 psi)

---

**Vacuum resistance**

0 mbar abs.

---

**Max. Turn down**

100:1

---

**Max. overpressure limit**

40 bar (600 psi)

---

**Process connection**

Mounting clamp

---

**Material process membrane**

316L, AlloyC,

Gold-Rhodium

PE, FEP

---

**Material gasket**

Viton, EPDM, Kalrez, none

---

**Fill fluid**

Inert oil,

Synthetic oil

---

---

**Pressure****Material housing**316L, Die-cast aluminum

---

**Communication**

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

---

**Certificates / Approvals**ATEX, FM, CSA, CSA C/US, IEC Ex, INMETRO, NEPSI

---

**Safety approvals**SIL

---

**Design approvals**

EN10204-3.1

NACE MR0175

---

**Marine approvals**GL/ ABS/ LR/ BV/ DNV

---

**Drinking water approvals**KTW/ NSF/ ACS

---

**Specialities**Modularity to differential pressure and process pressure devices  
(replacable display, universal electronics)Diagnostic functions

---

**Continuous / Liquids****Measuring principle**Hydrostatic

---

## Continuous / Liquids

### Characteristic / Application

Pressure transmitter for hydrostatic level measurement with flush mounted metallic Contite measuring cell:

Hermetically sealed, condensate-resistant and climatic-proofed

Cable version with suspension clamp

### Specialities

Modularity to differential pressure and process pressure devices (replacable display, universal electronics)

diagnostic functions

Hermetically sealed Contite measuring cell (condensate-resistant and climatic-proofed)

### Supply / Communication

4...20mA HART:

10,5...45V DC

Ex ia: 10,5...30V DC

PROFIBUS PA /

FOUNDATION Fieldbus:

9...32V DC (Non Ex)

### Accuracy

Standard 0.2%

Optional 0.1%

### Long term stability

0.05 % of URL/year

### Ambient temperature

-40°C...85°C

(-40°F...185°F)

---

**Continuous / Liquids****Process temperature**

PE cable: -10°C...70°C / 14°F...158°F

FEP cable: -10°C...80°C / 14°F...176°F

---

**Process pressure absolute / max. overpressure limit**

40 bar (600 psi)

---

**Pressure measuring range**

100mbar...10bar

(1.5psi...150psi)

---

**Main wetted parts**

Alloy C

316L

Cable (PE/FEP)

optional coating AuPt

optional coating AuRh

---

**Process connection**

Mounting clamp

---

**Max. measurement distance**100 m (328 ft) H<sub>2</sub>O

---

**Communication**

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

---

**Certificates / Approvals**

ATEX, FM, CSA, CSA C/US, IEC Ex, INMETRO, NEPSI

---

**Safety approvals**

SIL

## Continuous / Liquids

### Design approvals

EN10204-3.1

NACE MRO175

---

### Marine approval

GL/ ABS/ LR/ BV/ DNV

---

### Drinking water approvals

KTW/ NSF/ ACS

---

### Options

Initial device settings

Overvoltage protection

---

### Application limits

If pressurized, usage of two pressure transmitters to measure the differential pressure (electronic dP)

Observe ratio head pressure : hydrostatic pressure

---

More information [www.au.endress.com/FMB53](http://www.au.endress.com/FMB53)